

SACC-DSIV-FSD-4CON-L180 SCO - Device connector rear mounting



1542619

<https://www.phoenixcontact.com/us/products/1542619>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, Socket, straight, M12-SPEEDCON, D-coding, Wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1542619
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB26
Product key	ABQEHI
GTIN	4046356097888
Weight per piece (including packing)	12.62 g
Weight per piece (excluding packing)	9.728 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIV-FSD-4CON-L180 SCO - Device connector rear mounting



1542619

<https://www.phoenixcontact.com/us/products/1542619>

Technical data

Mounting

Mounting type	Rear mounting (M12 x 1, with flat nut)
---------------	--

Product properties

Product type	Circular connectors (device side)
Application	Data
	Signal
Number of positions	4
Shielded	yes
Coding	D
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Contact carrier	PA 6.6
Material Contact	CuZn
Material Contact surface	Ni/Au
Material Seal	FKM / EPDM
Flammability rating according to UL 94	V0

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

SACC-DSIV-FSD-4CON-L180 SCO - Device connector rear mounting



1542619

<https://www.phoenixcontact.com/us/products/1542619>

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	D

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

SACC-DSIV-FSD-4CON-L180 SCO - Device connector rear mounting



1542619

<https://www.phoenixcontact.com/us/products/1542619>

Drawings

Schematic diagram



Pin assignment M12 socket, 4-pos., D-coded, female side

SACC-DSIV-FSD-4CON-L180 SCO - Device connector rear mounting




1542619

<https://www.phoenixcontact.com/us/products/1542619>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1542619>

 UL Recognized Approval ID: E118976-20100522		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		250 V	4 A	22	-

SACC-DSIV-FSD-4CON-L180 SCO - Device connector rear mounting



1542619

<https://www.phoenixcontact.com/us/products/1542619>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-FSD-4CON-L180 SCO - Device connector rear mounting



1542619

<https://www.phoenixcontact.com/us/products/1542619>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b5420750-f1aa-403e-82e0-1f78af788052

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com