

SACB-4/ 8-L-C GG SCO - Distributor box header



1516739

<https://www.phoenixcontact.com/us/products/1516739>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box header, application: Standard, extended requirements, connection method: M12 socket Metal, number of slots: 4, number of positions: 5, coding: A, slot assignment: Double, status display: yes, PNP; master cable connection: Pluggable screw connection, shielding: no

Commercial data

Item number	1516739
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF42
Product key	AF3CCD
GTIN	4017918967468
Weight per piece (including packing)	197.6 g
Weight per piece (excluding packing)	175.5 g
Customs tariff number	85366990
Country of origin	DE

SACB-4/ 8-L-C GG SCO - Distributor box header



1516739

<https://www.phoenixcontact.com/us/products/1516739>

Height	26 mm
Length	117 mm

Material specifications

Material Threaded sleeve	Die-cast zinc
Material Housing	PBT
Material Molding compound	PUR
Flammability rating according to UL 94	V0
Seal material O-ring	NBR
Contact material	Cu alloy
Contact surface material	gold-plated
Contact carrier material	PA
Material of contact, master cable side	CU alloy
Material of the contact carrier on the master cable side	PA 6.6 V0
Material of contact surface, master cable side	gold-plated

Cable/line

Connection method	Pluggable screw connection
-------------------	----------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP69K
Ambient temperature (operation)	-30 °C ... 80 °C

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


SACB-4/ 8-L-C GG SCO - Distributor box header

1516739


<https://www.phoenixcontact.com/us/products/1516739>

Drawings

Dimensional drawing



Schematic diagram



M12 slot, socket, 5-pos.

SACB-4/ 8-L-C GG SCO - Distributor box header

1516739

<https://www.phoenixcontact.com/us/products/1516739>

Schematic diagram



Potential U_{N1} and U_{N2} bridged. Potential assignment: $U_{N1} = U_{N2} = \text{slots } 1,2,3,4$.

SACB-4/ 8-L-C GG SCO - Distributor box header

1516739

<https://www.phoenixcontact.com/us/products/1516739>

Schematic diagram



Electrically isolated. Potential assignment: U_{N1} = slots 1,3 and U_{N2} = slots 2,4.

SACB-4/ 8-L-C GG SCO - Distributor box header



1516739

<https://www.phoenixcontact.com/us/products/1516739>

Circuit diagram



SACB-4/ 8-L-C GG SCO - Distributor box header



1516739

<https://www.phoenixcontact.com/us/products/1516739>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1516739>

 cUL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	24 V	3 A	-	-

 UL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	24 V	3 A	-	-

SACB-4/ 8-L-C GG SCO - Distributor box header



1516739

<https://www.phoenixcontact.com/us/products/1516739>

Classifications

ECLASS

ECLASS-13.0	27440111
ECLASS-15.0	27440111

ETIM

ETIM 10.0	EC003558
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SACB-4/ 8-L-C GG SCO - Distributor box header



1516739

<https://www.phoenixcontact.com/us/products/1516739>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com