

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/us/products/1517877>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, INTERBUS (16 Mbps), 5-position, PUR halogen-free, may green RAL 6017, shielded, Plug straight M12 SPEEDCON, coding: B, on free cable end, cable length: 2 m

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1517877 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF04 |
| Product key | AF1CKB |
| GTIN | 4017918967994 |
| Weight per piece (including packing) | 166.5 g |
| Weight per piece (excluding packing) | 166.5 g |
| Customs tariff number | 85444290 |
| Country of origin | PL |

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/us/products/1517877>

Technical data

Product properties

| | |
|----------------------|-------------------------|
| Product type | Data cable preassembled |
| Application | Standard |
| Sensor type | INTERBUS |
| Number of positions | 5 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Coding | B |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Interfaces

| | |
|----------------------|-------------------|
| Bus system | INTERBUS |
| Signal type/category | INTERBUS, 16 Mbps |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Electrical properties

| | |
|-----------------------|----------|
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |
| Nominal current I_N | 4 A |
| Transmission medium | Copper |
| Transmission speed | 16 Mbps |

Material specifications

| | |
|--|---|
| Flammability rating according to UL 94 | V0 |
| Material of grip body | TPU, hardly inflammable, self-extinguishing |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | PA 6.6 |
| Material for screw connection | Zinc die-cast, nickel-plated |

Connection data

Connection assignment

| | |
|---|--------------------|
| Contact Color (signal designation) Contact (optional) | 1 (Plug) YE (DO) |
| | 2 (Plug) GN (DO) |
| | 3 (Plug) GY (DI) |

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/us/products/1517877>

| | |
|--|---------------------|
| | 4 (Plug) PK (DI) |
| | 5 (Plug) BN (GND) |

Connector

Connection 1

| | |
|---------------------|----------------------------|
| Type | Plug straight M12 SPEEDCON |
| Number of positions | 5 |
| Locking type | SPEEDCON |
| Coding type | B (inverse) |


Connection 2

| | |
|------|----------------|
| Type | free cable end |
|------|----------------|

Cable/line

| | |
|--------------|-----|
| Cable length | 2 m |
|--------------|-----|

INTERBUS [900]

| | |
|---------------------------------|--|
| Dimensional drawing |  |
| Cable weight | 70 kg/km |
| Number of positions | 6 |
| Shielded | yes |
| Cable type | INTERBUS [900] |
| Conductor structure | 3 x 2 x 0.22 mm ² |
| Signal speed | 0.66 c |
| Conductor structure signal line | 32x 0.10 mm |
| AWG signal line | 24 |
| Conductor cross-section | 3x 2x 0.22 mm ² |
| External cable diameter | 8.00 mm |
| Outer sheath, material | PUR |
| External sheath, color | may green RAL 6017 |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | PE |
| Single wire, color | green-yellow, white-brown, gray-pink |
| Twisted pairs | 2 cores to the pair |
| Overall twist | 3 pairs to the core |
| Insulation resistance | ≥ 5 GΩ*km |
| Coupling resistance | < 250.00 mΩ/m (at 30 MHz) |

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/us/products/1517877>

| | |
|---|---|
| Loop resistance | ≤ 159.80 Ω/km |
| Wave impedance | 120 Ω ±20 % (at 64 kHz) |
| | 100 Ω ±15 % (with 1 MHz) |
| Cable capacity | ≤ 60 nF/km (At 800 Hz) |
| Nominal voltage, cable | 250 V (Peak value, not for high-power applications) |
| Test voltage Core/Core | 1500 V _{rms} |
| Test voltage Core/Shield | 1000.00 V _{rms} |
| Minimum bending radius, fixed installation | 7.5 x D |
| Minimum bending radius, flexible installation | 15 x D |
| Smallest bending radius, fixed installation | 60 mm |
| Smallest bending radius, movable installation | 120 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000000, Bending radius: 120 mm, Traversing path: 10 m, Traversing rate: 1.6 m/s, Acceleration: 3.2 m/s ² |
| Near end crosstalk attenuation (NEXT) | ≥ 61 dB (at 772 kHz) |
| | ≥ 59 dB (with 1 MHz) |
| | ≥ 55 dB (at 2 MHz) |
| | ≥ 50 dB (at 4 MHz) |
| | ≥ 46 dB (at 8 MHz) |
| | ≥ 44 dB (at 10 MHz) |
| | ≥ 41 dB (at 16 MHz) |
| | ≥ 40 dB (at 20 MHz) |
| Shield attenuation | ≤ 15 dB/km (at 256 kHz) |
| | ≤ 24 dB/km (at 772 kHz) |
| | ≤ 27 dB/km (with 1 MHz) |
| | ≤ 52 dB/km (at 4 MHz) |
| | ≤ 84 dB/km (at 10 MHz) |
| | ≤ 112 dB/km (at 16 MHz) |
| | ≤ 119 dB/km (at 20 MHz) |
| Flame resistance | according to VDE 0472, Part 4, test type B |
| | according to IEC 60332-1 |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation) |
| | -30 °C ... 70 °C (Cable, flexible installation) |

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/us/products/1517877>

Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

1517877


<https://www.phoenixcontact.com/us/products/1517877>

Schematic diagram



Pin assignment M12 male connector, 5-pos., B-coded, male side

Circuit diagram



Contact assignment of the M12 plug

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/us/products/1517877>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1517877>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/us/products/1517877>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-5P-MSB/ 2,0-900 SCO - Bus system cable



1517877

<https://www.phoenixcontact.com/us/products/1517877>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.868 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com