

SAC-4P-M 8MS/ 5,0-950/M 8FS - Bus system cable



1543362

<https://www.phoenixcontact.com/us/products/1543362>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, INTERBUS, 4-position, PUR halogen-free, black RAL 9005, shielded, Plug straight M8, coding: A, on Socket straight M8, coding: A, cable length: 5 m

Your advantages

- Power cable for actuator voltage
- System cable for supply voltage and bus signal

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1543362 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF02 |
| Product key | AF1BJB |
| GTIN | 4046356097529 |
| Weight per piece (including packing) | 229.3 g |
| Weight per piece (excluding packing) | 220.7 g |
| Customs tariff number | 85444290 |
| Country of origin | PL |

SAC-4P-M 8MS/ 5,0-950/M 8FS - Bus system cable



1543362

<https://www.phoenixcontact.com/us/products/1543362>

Technical data

Product properties

| | |
|----------------------|-------------------------|
| Product type | Data cable preassembled |
| Application | Standard |
| Number of positions | 4 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Coding | A |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Interfaces

| | |
|----------------------|----------|
| Bus system | INTERBUS |
| Signal type/category | INTERBUS |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Electrical properties

| | |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |
| Nominal current I_N | 4 A |
| Test voltage | 800 V |
| Transmission medium | Copper |

Material specifications

| | |
|--|---|
| Flammability rating according to UL 94 | HB |
| Seal material | NBR |
| Material of grip body | TPU, hardly inflammable, self-extinguishing |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | TPU GF |
| Material for screw connection | Zinc die-cast, nickel-plated |

Connection data

Connection assignment

| | |
|---|--|
| Contact Color (signal designation) Contact (optional) | 1 (Plug) RD (0.34 mm ²) 1 (Socket) |
| | 3 (Plug) BU (0.34 mm ²) 3 (Socket) |
| | 2 (Plug) YE (0.14 mm ²) 2 (Socket) |

SAC-4P-M 8MS/ 5,0-950/M 8FS - Bus system cable



1543362

<https://www.phoenixcontact.com/us/products/1543362>

4 (Plug) | GN (0.14 mm²) | 4 (Socket)

Connector

Connection 1

| | |
|---------------------|------------------|
| Type | Plug straight M8 |
| Number of positions | 4 |
| Coding type | A (Standard) |

Connection 2

| | |
|---------------------|--------------------|
| Type | Socket straight M8 |
| Number of positions | 4 |
| Coding type | A |

Cable/line

| | |
|--------------|-----|
| Cable length | 5 m |
|--------------|-----|

INTERBUS [950]

| | |
|-------------------------------------|---|
| Cable weight | 41 kg/km |
| UL AWM Style | 20963 (80°C/30 V) |
| Number of positions | 4 |
| Shielded | yes |
| Cable type | INTERBUS [950] |
| Conductor structure | 2xAWG26/19+2xAWG22/19 |
| Conductor structure signal line | 19x 0.10 mm |
| AWG signal line | 26 |
| Conductor structure, voltage supply | 19x 0.15 mm |
| AWG power supply | 22 |
| Conductor cross-section | 2x 0.14 mm ² (Signal line) 2x 0.34 mm ² (Power supply) 1x 0.38 mm ² (Drain wire) |
| Wire diameter incl. insulation | 0.97 mm (Signal line) 1.25 mm (Power supply) |
| External cable diameter | 5.20 mm ±0.2 mm |
| Outer sheath, material | PUR |
| External sheath, color | black RAL 9005 |
| Conductor material | Tin-plated Cu litz wires |
| Material wire insulation | PP |
| Single wire, color | red-blue, green-yellow |
| Thickness, insulation | 0.24 mm (Conductor insulation, signal line) 0.25 mm (Conductor insulation, voltage supply) |
| Thickness, outer sheath | approx. 0.75 mm |
| Twisted pairs | 2 cores to the pair |
| Type of pair shielding | Aluminum-lined polyester foil |
| Overall twist | 2 pairs around a drain wire in the center to the core |
| Optical shield covering | 85 % |

SAC-4P-M 8MS/ 5,0-950/M 8FS - Bus system cable



1543362

<https://www.phoenixcontact.com/us/products/1543362>

| | |
|---|--|
| Max. conductor resistance | ≤ 150 Ω/km (Signal line) |
| | ≤ 58 Ω/km (Power supply) |
| Insulation resistance | ≥ 20 MΩ*km |
| Wave impedance | 75 Ω ±10 Ω (Signal line) |
| | 55 Ω ±10 Ω (Power supply) |
| Nominal voltage, cable | ≤ 100 V |
| Test voltage Core/Core | 1000 V (50 Hz, 1 min.) |
| Test voltage Core/Shield | 1000.00 V (50 Hz, 1 min.) |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 7.5 x D |
| Smallest bending radius, fixed installation | 26 mm |
| Smallest bending radius, movable installation | 39 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 1000000, Bending radius: 110 mm, Traversing path: 6 m, Traversing rate: 4 m/s, Acceleration: 4 m/s ² |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation) |
| | -40 °C ... 80 °C (Cable, flexible installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|----------------------------------|
| Degree of protection | IP65 |
| | IP67 |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket) |

SAC-4P-M 8MS/ 5,0-950/M 8FS - Bus system cable



1543362

<https://www.phoenixcontact.com/us/products/1543362>

Drawings

Dimensional drawing



Plug M8 x 1, straight, shielded

Dimensional drawing



Socket M8 x 1, straight, shielded

1543362

<https://www.phoenixcontact.com/us/products/1543362>

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side

SAC-4P-M 8MS/ 5,0-950/M 8FS - Bus system cable



1543362

<https://www.phoenixcontact.com/us/products/1543362>

Circuit diagram



Contact assignment of M8 plugs/sockets

SAC-4P-M 8MS/ 5,0-950/M 8FS - Bus system cable



1543362

<https://www.phoenixcontact.com/us/products/1543362>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1543362>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387



cULus Listed

Approval ID: E221474

SAC-4P-M 8MS/ 5,0-950/M 8FS - Bus system cable



1543362

<https://www.phoenixcontact.com/us/products/1543362>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-4P-M 8MS/ 5,0-950/M 8FS - Bus system cable



1543362

<https://www.phoenixcontact.com/us/products/1543362>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 2.698 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com