

# SAC-5P-MS/ 0,3-186/FS SCO - Sensor/actuator cable



1518407

<https://www.phoenixcontact.com/us/products/1518407>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PUR, black-gray RAL 7021, Plug straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A, cable length: 0.3 m

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Save time, thanks to installation with SPEEDCON fast locking system
- High-performance: connectors and cables with a large conductor cross-section for power supply

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1518407       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF03          |
| Product key                          | AF1CDA        |
| GTIN                                 | 4017918968526 |
| Weight per piece (including packing) | 45.3 g        |
| Weight per piece (excluding packing) | 43.5 g        |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 5                     |
| No. of cable outlets | 1                     |
| Shielded             | no                    |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|  |   |
|--|---|
| Flammability rating according to UL 94 | HB  |
| Seal material                          | NBR   |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn  |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 48 V AC                    |
|                       | 60 V DC                    |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connector

#### Connection 1

|                     |                            |
|---------------------|----------------------------|
| Type                | Plug straight M12 SPEEDCON |
| Number of positions | 5                          |
| Locking type        | SPEEDCON                   |
| Coding type         | A                          |

# SAC-5P-MS/ 0,3-186/FS SCO - Sensor/actuator cable



1518407

<https://www.phoenixcontact.com/us/products/1518407>


## Connection 2

|                     |                              |
|---------------------|------------------------------|
| Type                | Socket straight M12 SPEEDCON |
| Number of positions | 5                            |
| Locking type        | SPEEDCON                     |
| Coding type         | A                            |

## Cable/line

|              |       |
|--------------|-------|
| Cable length | 0.3 m |
|--------------|-------|

## PUR POWER 0.75 mm<sup>2</sup> black [186]

|   |   |
|---|---|
| Dimensional drawing                           |    |
| Cable weight                                  | 67 kg/km  |
| Number of positions                           | 5   |
| Shielded                                      | no  |
| Cable type                                    | PUR POWER 0.75 mm <sup>2</sup> black [186]  |
| Conductor structure signal line               | 42x 0.15 mm   |
| AWG signal line                               | 18  |
| Conductor cross-section                       | 5x 0.75 mm <sup>2</sup> (power line)  |
| Wire diameter incl. insulation                | 1.7 mm ±0.05 mm   |
| External cable diameter                       | 6.30 mm ±0.2 mm   |
| Outer sheath, material                        | PUR   |
| External sheath, color                        | black-gray RAL 7021   |
| Conductor material                            | Bare Cu litz wires  |
| Material wire insulation                      | PVC   |
| Single wire, color                            | brown, white, blue, black, gray   |
| Thickness, insulation                         | ≥ 0.23 mm (Core insulation)<br>≥ 0.76 mm (Outer cable sheath)   |
| Overall twist                                 | 5 wires around filler to the core   |
| Max. conductor resistance                     | max. 26 Ω/km (at 20 °C)   |
| Insulation resistance                         | ≥ 1 MΩ*km (at 20 °C)  |
| Nominal voltage, cable                        | ≤ 300 V   |
| Test voltage                                  | ≥ 3000 V  |
| Smallest bending radius, movable installation | 63 mm   |
| Dynamic load capacity (bending)               | Max. bending cycles: 2000000, Bending radius: 63 mm, Traversing path: 5 m, Traversing rate: 3 m/s, Acceleration: 5 m/s <sup>2</sup> |
| Flame resistance                              | in accordance with DIN UL-Style 20549   |
| Resistance to oil                             | in accordance with DIN EN 60811-2-1   |

# SAC-5P-MS/ 0,3-186/FS SCO - Sensor/actuator cable



1518407

<https://www.phoenixcontact.com/us/products/1518407>

|                                 |  |
|---------------------------------|--|
| Ambient temperature (operation) | -25 °C ... 80 °C (cable, fixed installation)   |
|                                 | -5 °C ... 80 °C (Cable, flexible installation) |

## Environmental and real-life conditions

### Ambient conditions

|   |  |
|---|--|
| Degree of protection  | IP65   |
|   | IP67   |
|   | IP68   |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket)               |
| Ambient temperature (operation) (Cable, fixed installation)       | -25 °C ... 80 °C (cable, fixed installation)   |
| Ambient temperature (operation) (Cable, flexible installation)    | -5 °C ... 80 °C (Cable, flexible installation) |

## Standards and regulations

### M12

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |

## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



M12 x 1 socket, straight

1518407

<https://www.phoenixcontact.com/us/products/1518407>

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

1518407

<https://www.phoenixcontact.com/us/products/1518407>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

# SAC-5P-MS/ 0,3-186/FS SCO - Sensor/actuator cable



1518407

<https://www.phoenixcontact.com/us/products/1518407>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1518407>

|  <b>UL Listed</b><br>Approval ID: FILE E 221474 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 125 V                 | 4 A                   | -                 | -                           |

|  <b>cUL Listed</b><br>Approval ID: FILE E 221474 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 125 V                 | 4 A                   | -                 | -                           |

|  <b>EAC-RoHS</b><br>Approval ID: RU D-DE.HB35.B.00387 |  |  |  |  |
|--|--|--|--|--|
|--|--|--|--|--|

1518407

<https://www.phoenixcontact.com/us/products/1518407>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

1518407

<https://www.phoenixcontact.com/us/products/1518407>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.366 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)