

HC-CME-DD-107-F-SNAP-L - Conductor connector



1549644

<https://www.phoenixcontact.com/us/products/1549644>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor connector, number of positions: 107+PE, number of connections per position: 1, Socket, Crimp connection, 250 V, 10 A, 0.14 mm² ... 2.5 mm², for connections in control cabinets

Commercial data

Item number	1549644
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF61
Product key	AF7ABZ
GTIN	4067923024946
Weight per piece (including packing)	90.2 g
Weight per piece (excluding packing)	90.2 g
Customs tariff number	85389099
Country of origin	CN

Technical data

Notes

General	Connectors may be operated only when there is no load/voltage.
General	It is imperative that the supplied funnel pads (HC-DD....FP) are used to prevent tip collision due to misalignment.

Mounting

Assembly note	Use within a control cabinet that is protected against unauthorized access is essential to ensure correct use. At the installation location in the control cabinet, the cable bundle to be connected must be properly installed and fitted with strain relief. As the pin connector pattern does not provide a leading protective conductor contact (PE), consistent grounding must be ensured by the control cabinet assembly.
---------------	---

Product properties

Product type	Contact insert with a fixed no. of positions
Number of positions	107
Connection profile	107+PE
Number of connections per position	1
Contact material type	turned
	rolled

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Dimensions

Mechanical characteristics

Contact diameter	1.6 mm
------------------	--------

Connection data

Connection technology

Connection technology	Crimp connection
Number of connections per position	1

Conductor connection

Conductor cross-section	0.14 mm ² ... 2.5 mm ²
Connection cross section AWG	26 ... 14
Stripping length of the individual wire	8 mm (0.14 mm ² ... 1.5 mm ²)
	6 mm (2.5 mm ²)

Electrical properties

Rated voltage (III/3)	250 V
Rated surge voltage	4 kV

HC-CME-DD-107-F-SNAP-L - Conductor connector



1549644

<https://www.phoenixcontact.com/us/products/1549644>

Rated current	10 A
---------------	------

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
---------------------------------	--

HC-CME-DD-107-F-SNAP-L - Conductor connector


1549644

<https://www.phoenixcontact.com/us/products/1549644>



Drawings


Dimensional drawing



1549644

<https://www.phoenixcontact.com/us/products/1549644>

Schematic diagram



Connector pin assignment, connection side

HC-CME-DD-107-F-SNAP-L - Conductor connector



1549644

<https://www.phoenixcontact.com/us/products/1549644>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1549644>

 cULus Recognized Approval ID: E468743				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	250 V	7 A	- 14	-

HC-CME-DD-107-F-SNAP-L - Conductor connector



1549644

<https://www.phoenixcontact.com/us/products/1549644>

Classifications

ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

ETIM

ETIM 10.0	EC000438
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

HC-CME-DD-107-F-SNAP-L - Conductor connector



1549644

<https://www.phoenixcontact.com/us/products/1549644>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com