

SAC-3P-M12FR-2L/500/5,0 GYIN - Sensor/actuator cable



1550371

<https://www.phoenixcontact.com/us/products/1550371>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, gray RAL 7001, free cable end, on Socket angled M12, with 2 LEDs, cable length: 5 m

Commercial data

Item number	1550371
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	AF1CBA
GTIN	4046356147224
Weight per piece (including packing)	222.22 g
Weight per piece (excluding packing)	222.22 g
Country of origin	PL

SAC-3P-M12FR-2L/500/5,0 GYIN - Sensor/actuator cable

1550371

<https://www.phoenixcontact.com/us/products/1550371>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	3
Shielded	no

Electrical properties

Nominal voltage U_N	24 V DC
-----------------------	---------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2


Type	Socket angled M12
Number of positions	3

Cable/line

Cable length	5 m
--------------	-----

PVC gray [500]

Dimensional drawing



Cable weight	40 kg/km
UL AWM Style	2464 / 1729 (80°C/300 V)
Number of positions	3
Shielded	no
Cable type	PVC gray [500]
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor cross-section	3x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.26 mm \pm 0.05 mm

SAC-3P-M12FR-2L/500/5,0 GYIN - Sensor/actuator cable



1550371

<https://www.phoenixcontact.com/us/products/1550371>

External cable diameter	4.30 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm
Overall twist	3 wires, twisted
Max. conductor resistance	max. 57 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 2500 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	22 mm
Smallest bending radius, movable installation	43 mm
Flame resistance	As per UL-Style 2464
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


SAC-3P-M12FR-2L/500/5,0 GYIN - Sensor/actuator cable

1550371

<https://www.phoenixcontact.com/us/products/1550371>

Drawings

Circuit diagram



SAC-3P-M12FR-2L/500/5,0 GYIN - Sensor/actuator cable



1550371

<https://www.phoenixcontact.com/us/products/1550371>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

SAC-3P-M12FR-2L/500/5,0 GYIN - Sensor/actuator cable



1550371

<https://www.phoenixcontact.com/us/products/1550371>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com