

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable



1550708

<https://www.phoenixcontact.com/us/products/1550708>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

By the meter, Sensor/actuator cable, shielded, PVC, black RAL 9005, 8-wire, color single wire: white, brown, green, yellow, gray, pink, blue, red, cable length: 100 m



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1550708 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF11 |
| Product key | AF1LBA |
| GTIN | 4046356170512 |
| Weight per piece (including packing) | 8,950 g |
| Weight per piece (excluding packing) | 6,608 g |
| Customs tariff number | 85444995 |
| Country of origin | DE |

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable



1550708

<https://www.phoenixcontact.com/us/products/1550708>

Technical data


Product properties

| | |
|---------------------|--------------------|
| Product type | Cable by the meter |
| Application | Connector |
| Number of positions | 8 |
| Shielded | yes |

Cable/line

| | |
|--------------|-------|
| Cable length | 100 m |
|--------------|-------|

PVC black [PVC]

| | |
|---------------------------------|---|
| Dimensional drawing |  |
| Note | The cable is not suitable for use with drag chains. |
| Cable weight | 85 kg/km |
| UL AWM Style | 2517 |
| Number of positions | 8 |
| Shielded | yes |
| Cable type | PVC black [PVC] |
| Conductor structure signal line | 32x 0.10 mm |
| AWG signal line | 24 |
| Conductor cross-section | 8x 0.25 mm ² (Signal line) |
| Wire diameter incl. insulation | 1.5 mm ±0.05 mm (Signal line) |
| External cable diameter | 7.70 mm ±0.2 mm |
| Outer sheath, material | PVC |
| External sheath, color | black RAL 9005 |
| Conductor material | Bare Cu litz wires |
| Material, filler | PVC |
| Material wire insulation | PVC |
| Single wire, color | white, brown, green, yellow, gray, pink, blue, red |
| Thickness, insulation | ≥ 0.38 mm (Conductor insulation, signal line) ≥ 0.76 mm (Outer cable sheath) |
| Overall twist | 8 wires around filler to the core, twisted in with additional Cu litz in the wire outer godet |
| Optical shield covering | 85 % |
| Max. conductor resistance | ≤ 78 Ω/km |
| Insulation resistance | ≥ 10 GΩ*km |

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable



1550708

<https://www.phoenixcontact.com/us/products/1550708>

| | |
|---|---|
| Nominal voltage, cable | 300 V |
| Test voltage | 3000 V |
| Smallest bending radius, fixed installation | 38.5 mm |
| Smallest bending radius, movable installation | 77 mm |
| Flame resistance | According to UL 758/1581 (Cable Flame) |
| | According to DIN EN 60332-1-2 (60 s) |
| Resistance to oil | According to DIN EN 60811-2-1, 168 h at 80°C |
| Ambient temperature (operation) | -25 °C ... 105 °C (cable, fixed installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) (Cable, fixed installation) | -25 °C ... 80 °C (cable, fixed installation) |
| Ambient temperature (operation) (Cable, flexible installation) | -5 °C ... 80 °C (Cable, flexible installation) |

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable





1550708


<https://www.phoenixcontact.com/us/products/1550708>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1550708>

|  UL Listed Approval ID: FILE E 221474 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 30 V | 2 A | - | - |

|  cUL Listed Approval ID: FILE E 221474 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 30 V | 2 A | - | - |

|  EAC-RoHS Approval ID: RU D-DE.HB35.B.00371 | |
|--|--|
|--|--|

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable



1550708

<https://www.phoenixcontact.com/us/products/1550708>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27061801 |
| ECLASS-15.0 | 27061801 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003249 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable



1550708

<https://www.phoenixcontact.com/us/products/1550708>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|----------------|
| CO2e kg | 71.767 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com