

AXC F 2000 EA - Controller



1551772

<https://www.phoenixcontact.com/us/products/1551772>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Controller (SPS), PLCnext Control; Programming: High-level language and IEC 61131-3; Operating system: Yocto/Linux® (real-time); Programming tool: PLCnext Engineer, Eclipse®, Visual Studio®, MATLAB®/ Simulink®; Product certified in accordance with IEC 62351-3 and IEC 62443 (SL2) (Certification conditions see user documentation); Processor: Arm® Cortex®-A53, 3x 1.2 GHz.

Your advantages

- Real-time-capable Linux operating system for deterministic and reliable execution of time-critical processes
- Developed for the field of energy applications
- Numerous protocols supported such as: http, https, FTP, SNMP, IPsec, syslog
- Contains licenses for IEC 60870-5-101/-104 and Modbus/RTU
- Supports common fieldbus protocols (IEC 60870-5-101/-104, IEC 61850, Modbus TCP/RTU, Ethernet TCP/IP, etc.), for integration into existing energy technology systems and installations.
- Maximum design freedom thanks to the combination of classic PLC programming with modern high-level languages such as C++, C#, or Python
- Meets the highest security requirements of industrial automation – for the protection of your applications and data
- Specially developed Axioline Smart Elements for maximum flexibility and scalability
- 3 independent Ethernet interfaces
- Meets increased requirements in accordance with IEC 61850-3 Class H
- Extended temperature range of -40 °C ... +70 °C
- Integrated cybersecurity meets security standards in accordance with IEC 62443 and IEC 62351-3

Commercial data

Item number	1551772
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR09
Product key	DRMBAA
GTIN	4067923029323
Weight per piece (including packing)	422.7 g
Weight per piece (excluding packing)	356.8 g
Customs tariff number	85371091
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Controller
Product family	PLCnext Control
Type	modular
Special properties	Product certified in accordance with IEC 62351-3 and IEC 62443 (SL2) Certification conditions see user documentation

Insulation characteristics

Protection class	II (IEC 61140, EN 61140, VDE 0140-1)
Overvoltage category	II (IEC 61010-2-201/EN IEC 61010-2-201)
Pollution degree	2

Display

Diagnostics display	no
---------------------	----

System properties

Trusted Platform Module	TPM 2.0
Flash memory	4 GByte (internal flash memory) SD card from Phoenix Contact (for external flash memory, see accessories)
Retentive data storage	1 Mbyte (NVRAM)

IEC 61131 runtime system

Program memory	12 Mbyte
Data storage system	32 Mbyte (internal flash memory)

Axioline

Amount of process data	max. 1482 Byte (per station (total input and output data))
	max. 1024 Byte (Axioline F local bus (input))
	max. 1024 Byte (Axioline F local bus (output))
Number of supported devices	max. 63 (per station)
Number of local bus devices that can be connected	max. 63 (observe current consumption)

INTERBUS-Master

Amount of process data (Axioline input/output data max.)	max. 1482 Byte (per station (total input and output data))
Amount of process data (Axioline input data max.)	max. 1024 Byte (Axioline F local bus (input))
Amount of process data (Axioline output data max.)	max. 1024 Byte (Axioline F local bus (output))

Function

Diagnostics display	no
---------------------	----

AXC F 2000 EA - Controller



1551772

<https://www.phoenixcontact.com/us/products/1551772>

Redundancy function	yes
Industrial cybersecurity	yes

Programming data

Register length (master)	148 Byte
--------------------------	----------

Functionality

Programming languages supported	Symbolic flowchart (SFC)
	Ladder diagram (LD)
	Function block diagram (FBD)
	Structured text (ST)
	C++
	C#
	Java
	Python®
Simulink®	

System requirements

Application interface	OPC UA®
-----------------------	---------

Electrical properties

Real-time clock

Realtime clock	yes
Description realtime clock	typ. 10 ppm, max. 20 ppm at 25°C

Potentials

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple (± 5 %))
Power consumption	max. 16.2 W
Protective circuit	Surge protection; electronic
	Reverse polarity protection; electronic

Potentials: Axioline F local bus supply (U_{Bus})

Supply voltage	5 V DC (via bus base module)
----------------	------------------------------

Output data

Relay

Number of outputs	1
Connection method	ST
Contact switching type	Single contact, 1 changeover contact
Contact connection type	Socket/pin

Interfaces

Supported protocols	HTTP
	HTTPS

1551772

<https://www.phoenixcontact.com/us/products/1551772>

	SFTP
	MQTT (via corresponding app)
	OPC UA® Server
	OPC UA® Client (via corresponding app)
	DHCP (via corresponding app)
	IEC 60870-5-101 (Via extension module)
	IEC 60870-5-104
	IEC 61850 (via corresponding library)
	Modbus/RTU
	Modbus/TCP (via corresponding library)
	IPsec
	syslog
	DHCP
Web server	yes

Axioline F local bus

Number of interfaces	1
Connection method	Bus base module
Transmission speed	100 Mbps

Ethernet

Bus system	RJ45
Number of interfaces	3
Connection method	RJ45 jack
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	100/1000/10000 Mbps (full duplex)
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	max. 100 m

Dimensions

Width	100 mm
Height	126.93 mm
Depth	75 mm
Note on dimensions	The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715).

Material specifications

Color (Housing)	gray (RAL 7042)
-----------------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (Manufacturers declaration, not evaluated by UL)
Ambient temperature (operation)	-40 °C ... 70 °C up to 2000 m above mean sea level (observe derating)
	-40 °C ... 70 °C up to 3000 m above mean sea level (≥ 55°C (at maximum 1 A at UBus), observe derating)

	55 °C ... 70 °C (Observe the requirements in the user manual for operation in the extended temperature range in accordance with IEC 61850-3.)
	-40 °C ... 70 °C (Observe the requirements in the user manual for operation in the extended temperature range in accordance with IEC 61850-3.)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	5 % ... 95 % (according to DIN EN 61131-2)
Shock (operation)	30g (in accordance with EN 60068-2-27/IEC 60068-2-27)
Vibration (operation)	5g (in accordance with EN 60068-2-6/IEC 60068-2-6)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	58 kPa ... 106 kPa (up to 4500 m above mean sea level)

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	Immunity test in accordance with EN IEC 61000-6-5 Electrostatic discharge (ESD) IEC 61000-4-2 Criterion A, 6 kV contact discharge, 8 kV air discharge
	Immunity test in accordance with EN IEC 61000-6-5 Electromagnetic fields IEC 61000-4-3 Criterion A, Field intensity: 10 V/m
	Immunity test in accordance with EN IEC 61000-6-5 Fast transients (burst) IEC 61000-4-4 Criterion A, 4 kV
	Immunity test in accordance with EN IEC 61000-6-5 Transient overvoltage (surge) IEC 61000-4-5 Criterion A, 4 kV asymmetrical, 2 kV symmetrical
	Immunity test in accordance with EN IEC 61000-6-5 Conducted interference IEC 61000-4-6 Criterion A, Test voltage 10 V
	Noise emission test in accordance with EN 61000-6-4/IEC 61000-6-4 pass

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

AXC F 2000 EA - Controller

1551772

<https://www.phoenixcontact.com/us/products/1551772>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1551772>



cULus Listed

Approval ID: E238705

AXC F 2000 EA - Controller

1551772

<https://www.phoenixcontact.com/us/products/1551772>



Classifications

ECLASS

ECLASS-13.0	27242207
ECLASS-15.0	27242207

1551772

<https://www.phoenixcontact.com/us/products/1551772>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	Lead(CAS: 7439-92-1)

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com