

# SACC-DSIV-M 8FS-4CON-L 90 - Device connector rear mounting



1526169

<https://www.phoenixcontact.com/us/products/1526169>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device connector rear mounting, 4-position, Socket, straight, M8, A-coding, Wave soldering



## Your advantages

- Standard pin assignments and codings for signal transmission with a uniform design-in design

## Commercial data

Item number	1526169
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB22
Product key	ABQJBG
GTIN	4017918953874
Weight per piece (including packing)	5.4 g
Weight per piece (excluding packing)	5.1 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSIV-M 8FS-4CON-L 90 - Device connector rear mounting



1526169

<https://www.phoenixcontact.com/us/products/1526169>

## Technical data

### Mounting

Mounting type	Rear mounting (M8 x 1, with locking nut)
---------------	--

### Product properties

Product type	Circular connectors (device side)
Number of positions	4
Shielded	no
Coding	A
Thread type	M8

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	CuSn
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	HB

### Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	50 V AC
	60 V DC
Nominal current $I_N$	4 A

### Connection data

#### Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

### Connector

#### Connection 1

Head design	Socket
Head cable outlet	straight

# SACC-DSIV-M 8FS-4CON-L 90 - Device connector rear mounting



1526169

<https://www.phoenixcontact.com/us/products/1526169>

Head thread type	M8
Coding	A

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C
Ambient temperature (operation)	-25 °C ... 85 °C
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104


# SACC-DSIV-M 8FS-4CON-L 90 - Device connector rear mounting

1526169

<https://www.phoenixcontact.com/us/products/1526169>

## Drawings

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side

# SACC-DSIV-M 8FS-4CON-L 90 - Device connector rear mounting



1526169

<https://www.phoenixcontact.com/us/products/1526169>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 10.0	EC003568
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSIV-M 8FS-4CON-L 90 - Device connector rear mounting



1526169

<https://www.phoenixcontact.com/us/products/1526169>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f46e2811-eeba-4a6b-875d-00a4b90aa9b3

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)