

IPD PL 5P2,5 M A1,0 F PVC GY - Connecting cable



1526889

<https://www.phoenixcontact.com/us/products/1526889>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connecting cable/ Push-lock connection, number of positions: 4+PE, Socket/pin, 450 V, 16 A, PA, light gray, coding: P, 2.5 mm², cable length: 1 m, Male straight, on Socket straight

Your advantages

- Easy distribution of power, as components are plugged directly
- Simple, time-saving wiring in the field with Push-Lock connection
- Reliable installation in harsh environments with IP66, IP68, and IP69K throughout the entire system
- Secure, tool-free locking even in particularly difficult installation situations
- Fast commissioning with preassembled cable assemblies

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1526889 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF51 |
| Product key | AF6NCA |
| GTIN | 4063151996581 |
| Weight per piece (including packing) | 378.7 g |
| Weight per piece (excluding packing) | 378.7 g |
| Customs tariff number | 85444290 |
| Country of origin | PL |

IPD PL 5P2,5 M A1,0 F PVC GY - Connecting cable



1526889

<https://www.phoenixcontact.com/us/products/1526889>

Technical data

Notes

| | |
|--------------------|---|
| General | NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
| Order information: | This item is also available with other cable lengths. For your specific requirements, please contact your local PHOENIX CONTACT subsidiary. |

Product properties

| | |
|------------------------------------|------------------------------|
| Product type | Assembled installation cable |
| Product family | IPD |
| Number of positions | 5 |
| Connection profile | 4+PE |
| Position marking | 1, 2, 3, N, PE |
| Number of connections per position | 1 |
| Coding | P |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties


| | |
|-----------------------------|--|
| Rated surge voltage (III/3) | 6 kV |
| Rated current | 16 A (in accordance with IEC 61984 at 25 °C ambient temperature) |
| Rated voltage (III/3) | 450 V (flexible installation) 600 V (Fixed, protected installation) |
| Nominal voltage U_N | 450 V AC/DC (flexible installation) 600 V AC/DC (Fixed, protected installation) |
| Nominal current I_N | 16 A (in accordance with IEC 61984 at 25 °C ambient temperature) |

Connection data

Connection technology

| | |
|-------------------------------------|----------------------|
| Connection method On the field side | Push-lock connection |
|-------------------------------------|----------------------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 32.5 mm |

IPD PL 5P2,5 M A1,0 F PVC GY - Connecting cable



1526889

<https://www.phoenixcontact.com/us/products/1526889>

| | |
|--------|---------|
| Height | 32.1 mm |
| Length | 91.6 mm |

Material specifications

| | |
|--------------------------|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
| Material Housing | PA |
| Material Seal | NBR |
| Contact material | Cu |
| Contact surface material | Ni/Ag/Sn |

Cable/line

| | |
|---|--|
| Cable length | 1 m |
| Structure of individual litz in acc. with VDE 0295 / smallest wire diameter | Class 5 in accordance with IEC 60228 |
| External cable diameter | 11.8 mm |
| Position marking | 1, 2, 3, N, PE |
| Single wire, color | Brown 1, black 2, gray 3, blue N, green-yellow PE |
| Cable cross section | 2.5 mm ² |
| Material wire insulation | PVC |
| Minimum bending radius, fixed installation | 4 x D |
| Minimum bending radius, flexible installation | 15 x D |
| Ambient temperature (operation) | -30 °C ... 80 °C (cable, fixed installation) -5 °C ... 70 °C (Cable, flexible installation) |

Mechanical properties

Mechanical data

| | |
|-----------------------------|------------------------------------|
| Insertion/withdrawal cycles | 50 (IP66/IP68/IP69K) 100 (IP66) |
|-----------------------------|------------------------------------|


Environmental and real-life conditions

Ambient conditions


| | |
|--|--|
| Degree of protection | IP66 IP68 (2 m / 24 h) IP69K (Distance from the nozzle 150 mm) Touch-proof when not plugged in (IP2X) |
| Impact strength | IK07 |
| Ambient temperature (operation) (Cable, flexible installation) | -5 °C ... 70 °C (Cable, flexible installation) |
| Ambient temperature (operation) (Cable, fixed installation) | -30 °C ... 80 °C (cable, fixed installation) |
| Ambient temperature (operation) | -30 °C ... 100 °C (Plug) |
| Temperature when conductor connected | -5 °C ... 50 °C |
| Resistance to UV radiation | no |

Drawings

Dimensional drawing




Dimensional drawing



1526889


<https://www.phoenixcontact.com/us/products/1526889>

Diagram



Derating diagram for cable, flexible installation

Diagram



Derating diagram for cable, fixed installation

IPD PL 5P2,5 M A1,0 F PVC GY - Connecting cable



1526889

<https://www.phoenixcontact.com/us/products/1526889>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440604 |
| ECLASS-15.0 | 27440604 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002587 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

IPD PL 5P2,5 M A1,0 F PVC GY - Connecting cable



1526889

<https://www.phoenixcontact.com/us/products/1526889>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com