

# SACC-DSIV-M12FSB-5CON-L 90 - Device connector rear mounting



1527870

<https://www.phoenixcontact.com/us/products/1527870>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device connector rear mounting, 5-position, Socket, angled, M12, B-coding, Wave soldering



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1527870       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | AB23          |
| Product key                          | ABQEHI        |
| GTIN                                 | 4046356011402 |
| Weight per piece (including packing) | 14.57 g       |
| Weight per piece (excluding packing) | 11.1 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | HU            |

# SACC-DSIV-M12FSB-5CON-L 90 - Device connector rear mounting



1527870

<https://www.phoenixcontact.com/us/products/1527870>

## Technical data

### Mounting

|               |   |
|---------------|---|
| Mounting type | Rear mounting (M12 x 1, with locking nut) |
|---------------|---|

### Product properties

|                     |                                   |
|---------------------|-----------------------------------|
| Product type        | Circular connectors (device side) |
| Number of positions | 5                                 |
| Shielded            | no                                |
| Coding              | B                                 |
| Thread type         | M12                               |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|  |        |
|--|--------|
| Material Housing                       | CuZn   |
| Material Housing surface               | Ni     |
| Material Contact carrier               | PA 6.6 |
| Material Contact                       | CuZn   |
| Material Contact surface               | Au     |
| Material Seal                          | NBR    |
| Flammability rating according to UL 94 | HB     |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Contact resistance    | $\leq 3 \text{ m}\Omega$   |
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 125 V                      |
| Nominal current $I_N$ | 4 A                        |

### Connection data

#### Conductor connection

|                         |                |
|-------------------------|----------------|
| Connection method       | Wave soldering |
| Contact connection type | Socket         |

### Connector

#### Connection 1

|                   |        |
|-------------------|--------|
| Head design       | Socket |
| Head cable outlet | angled |
| Head thread type  | M12    |
| Coding            | B      |

# SACC-DSIV-M12FSB-5CON-L 90 - Device connector rear mounting



1527870

<https://www.phoenixcontact.com/us/products/1527870>

## Environmental and real-life conditions

### Ambient conditions

|   |                          |
|---|--------------------------|
| Degree of protection  | IP67                     |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C         |
| UL Type Rating  | Type 4 (indoor use only) |

## Standards and regulations

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | M12 circular connector       |
| Standards/specifications | according to IEC 61076-2-101 |

# SACC-DSIV-M12FSB-5CON-L 90 - Device connector rear mounting



1527870

<https://www.phoenixcontact.com/us/products/1527870>

## Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side


SACC-DSIV-M12FSB-5CON-L 90 - Device connector rear mounting



1527870

<https://www.phoenixcontact.com/us/products/1527870>

Diagram



Attenuation curve of the SACC... male/female connectors

# SACC-DSIV-M12FSB-5CON-L 90 - Device connector rear mounting





1527870


<https://www.phoenixcontact.com/us/products/1527870>


## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1527870>

|  <b>cUL Recognized</b><br>Approval ID: FILE E 221474 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 60 V                  | 4 A                   | -                 | -                           |

|  <b>UL Recognized</b><br>Approval ID: FILE E 221474 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 60 V                  | 4 A                   | -                 | -                           |

|  <b>UL Recognized</b><br>Approval ID: E221474-20070307 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 60 V                  | 4 A                   | -                 | -                           |

|  <b>cUL Recognized</b><br>Approval ID: E221474-20070307 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 60 V                  | 4 A                   | -                 | -                           |

# SACC-DSIV-M12FSB-5CON-L 90 - Device connector rear mounting



1527870

<https://www.phoenixcontact.com/us/products/1527870>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440110 |
| ECLASS-15.0 | 27440110 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003568 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-DSIV-M12FSB-5CON-L 90 - Device connector rear mounting



1527870

<https://www.phoenixcontact.com/us/products/1527870>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | b95f2527-9ff9-47d9-b63b-de58afdb4dd5 |

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.972 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)