


SACC-V-3CON-PG9/A-1L-SV 24V - Valve connector



1527919

<https://www.phoenixcontact.com/us/products/1527919>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Valve connector, Universal, 3-position, Valve connector A, Screw connection, cable gland Pg9, external cable diameter 6 mm ... 8 mm

Commercial data

Item number	1527919
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF36
Product key	AF2DAA
GTIN	4017918980993
Weight per piece (including packing)	24.72 g
Weight per piece (excluding packing)	24.7 g
Customs tariff number	85366990
Country of origin	HU

SACC-V-3CON-PG9/A-1L-SV 24V - Valve connector



1527919

<https://www.phoenixcontact.com/us/products/1527919>

Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
---------------	---

Product properties

Product type	Valve connectors
Sensor type	Universal
Number of positions	3
No. of cable outlets	1
Shielded	no
Pg screw connection	Pg9

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material housing valve plug	PA 6
Contact material	CuSn
Valve plug contact insert material	PA 6
Contact surface material	Ni

Dimensions

External dimensions

Outside diameter	6 mm ... 8 mm
------------------	---------------

Electrical properties

Contact resistance	$\leq 15 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	24 V AC
	24 V DC
Nominal current I_N	10 A
Protective circuit	Surge protection; Varistor

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50 (Valve connector)
-----------------------------	----------------------

SACC-V-3CON-PG9/A-1L-SV 24V - Valve connector



1527919

<https://www.phoenixcontact.com/us/products/1527919>

Signaling

Status display	1 LED
Status display present	yes

Connection data

Connection method	Screw connection
Conductor cross-section	0.34 mm ² ... 1.5 mm ²
Connection cross section AWG	22 ... 16
Stripping length of the individual wire	6 mm
Tightening torque	0.8 Nm ... 1 Nm (Pressure nut)
	0.4 Nm (Central screw)
	0.5 Nm (Contact screw)

Connector

Connection 1

Head design	Valve connector
Head thread type	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Valve connector)


SACC-V-3CON-PG9/A-1L-SV 24V - Valve connector

1527919


<https://www.phoenixcontact.com/us/products/1527919>

Drawings

Dimensional drawing



Schematic diagram



Valve connector pin assignment, type A


SACC-V-3CON-PG9/A-1L-SV 24V - Valve connector



1527919

<https://www.phoenixcontact.com/us/products/1527919>

Circuit diagram



SACC-V-3CON-PG9/A-1L-SV 24V - Valve connector



1527919

<https://www.phoenixcontact.com/us/products/1527919>

Classifications

ECLASS

ECLASS-13.0	27440105
ECLASS-15.0	27440105

ETIM

ETIM 10.0	EC003623
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SACC-V-3CON-PG9/A-1L-SV 24V - Valve connector



1527919

<https://www.phoenixcontact.com/us/products/1527919>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0df2c1a2-63e1-42d5-9729-c1651830f760

EF3.1 Climate Change

CO2e kg	0.732 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com