

# SACC-DSIV-M12FS-4CON-L180-SI - Device connector rear mounting



1528154

<https://www.phoenixcontact.com/us/products/1528154>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, Socket, straight, M12, A-coding, Wave soldering, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1528154
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB26
Product key	ABQEHL
GTIN	4046356023139
Weight per piece (including packing)	22.08 g
Weight per piece (excluding packing)	16.082 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSIV-M12FS-4CON-L180-SI - Device connector rear mounting



1528154

<https://www.phoenixcontact.com/us/products/1528154>

## Technical data

### Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

### Mounting

Mounting type	Rear mounting (Pg9, with locking nut)
---------------	---------------------------------------

### Product properties

Product type	Circular connectors (device side)
Number of positions	4
Shielded	no
Coding	A
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Contact carrier	PBT
Material Contact	CuZn
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	V0

### Electrical properties

Contact resistance	$\leq 0.003 \Omega$
Insulation resistance	$\geq 100000 \Omega$
Nominal voltage $U_N$	250 V
Nominal current $I_N$	4 A

### Connection data

#### Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

### Connector

#### Connection 1

Head design	Socket
-------------	--------

# SACC-DSIV-M12FS-4CON-L180-SI - Device connector rear mounting



1528154

<https://www.phoenixcontact.com/us/products/1528154>

Head cable outlet	straight
Head thread type	M12
Coding	A

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
UL Type Rating	Type 4 (indoor use only)

# SACC-DSIV-M12FS-4CON-L180-SI - Device connector rear mounting

1528154

<https://www.phoenixcontact.com/us/products/1528154>

## Drawings

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

# SACC-DSIV-M12FS-4CON-L180-SI - Device connector rear mounting



1528154

<https://www.phoenixcontact.com/us/products/1528154>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1528154>

 <b>UL Recognized</b> Approval ID: E118976-20100522				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	250 V	4 A	22	-

# SACC-DSIV-M12FS-4CON-L180-SI - Device connector rear mounting



1528154

<https://www.phoenixcontact.com/us/products/1528154>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 10.0	EC003568
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSIV-M12FS-4CON-L180-SI - Device connector rear mounting



1528154

<https://www.phoenixcontact.com/us/products/1528154>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4d37f16e-9c6f-4d92-9d98-85b9a4db330f

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)