

SACC-CI-M12FS-5CON-SCO - Device connector rear mounting



1528280

<https://www.phoenixcontact.com/us/products/1528280>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Socket, straight, M12-SPEEDCON, A-coding, Wave soldering, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

Item number	1528280
Packing unit	100 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB23
Product key	ABQAGS
GTIN	4046356023252
Weight per piece (including packing)	8.27 g
Weight per piece (excluding packing)	8.074 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M12FS-5CON-SCO - Device connector rear mounting



1528280

<https://www.phoenixcontact.com/us/products/1528280>

Technical data

Mounting

Mounting type	Rear mounting
---------------	---------------

Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	no
Coding	A
Thread type	M12

Insulation characteristics

Degree of pollution	3
---------------------	---

Dimensions

PCB design

PCB thickness	1 mm
---------------	------

Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Contact carrier	PA 6
Material Contact	CuZn
Material Contact surface	Au
Material Seal	NBR (O-ring)
Flammability rating according to UL 94	HB

Electrical properties

Contact resistance	$\leq 0.003 \Omega$
Insulation resistance	\geq
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

Connector

Connection 1

Head design	Socket
-------------	--------

SACC-CI-M12FS-5CON-SCO - Device connector rear mounting



1528280

<https://www.phoenixcontact.com/us/products/1528280>

Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C
UL Type Rating	Type 4 (indoor use only)

SACC-CI-M12FS-5CON-SCO - Device connector rear mounting

1528280

<https://www.phoenixcontact.com/us/products/1528280>

Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

SACC-CI-M12FS-5CON-SCO - Device connector rear mounting





1528280

<https://www.phoenixcontact.com/us/products/1528280>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1528280>

 cUL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

 UL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

SACC-CI-M12FS-5CON-SCO - Device connector rear mounting



1528280

<https://www.phoenixcontact.com/us/products/1528280>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12FS-5CON-SCO - Device connector rear mounting



1528280

<https://www.phoenixcontact.com/us/products/1528280>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.301 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com