

# SACC-M12MRD-4Q SH - Data connector



1553624

<https://www.phoenixcontact.com/us/products/1553624>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Data connector, Ethernet CAT5 (100 Mbps), 4-position, shielded, Plug angled M12, coding: D, Insulation displacement connection, knurl material: Brass, nickel-plated, external cable diameter 4 mm ... 8 mm



## Your advantages

- Safe use in the field, thanks to a high degree of protection
- Insulation displacement connection: innovative and time-saving assembly without stripping the single wire
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1553624       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF31          |
| Product key                          | AF2CDI        |
| GTIN                                 | 4046356158794 |
| Weight per piece (including packing) | 38.4 g        |
| Weight per piece (excluding packing) | 38.4 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

1553624

<https://www.phoenixcontact.com/us/products/1553624>

## Technical data

### Notes

|               |   |
|---------------|---|
| Assembly note | <b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|---|

### Mounting

|               |   |
|---------------|---|
| Assembly note | The connector pin assignment can be rotated 45° to the cable outlet |
|---------------|---|


### Product properties

|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Application          | Data                            |
| Number of positions  | 4                               |
| No. of cable outlets | 1                               |
| Shielded             | yes                             |
| Coding               | D                               |
| Cable outlet         | angled                          |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 41 mm  |
| Height              | 19 mm  |
| Length              | 50 mm  |

### External dimensions

|                  |               |
|------------------|---------------|
| Outside diameter | 4 mm ... 8 mm |
|------------------|---------------|

### Material specifications

|  |                              |
|--|------------------------------|
| Flammability rating according to UL 94 | V0                           |
| Seal material                          | Neoprene                     |
| Material of grip body                  | Zinc die-cast, nickel-plated |
| Contact material                       | CuSn                         |
| Contact surface material               | Ni/Au                        |

# SACC-M12MRD-4Q SH - Data connector



1553624

<https://www.phoenixcontact.com/us/products/1553624>

|                               |                      |
|-------------------------------|----------------------|
| Contact carrier material      | PA 6                 |
| Material for screw connection | Brass, nickel-plated |

## Connection data

### Conductor connection

|                              |   |
|------------------------------|---|
| Connection method            | Insulation displacement connection            |
| Connection cross section     | 0.14 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> |
| Connection cross section AWG | 26 ... 22                                     |
| Tightening torque            | 0.4 Nm (M12 knurl)                            |
|                              | 0.8 Nm (Connector with coupling sleeve)       |
|                              | 3 Nm (Pressure nut with coupling sleeve)      |

### Connection assignment

|   |                       |
|---|-----------------------|
| Contact   Color (signal designation)   Contact (optional) | 1 (Plug) = OGWH (TD+) |
|   | 3 (Plug) = OG (TD-)   |
|   | 2 (Plug) = GNWH (RD+) |
|   | 4 (Plug) = GN (RD-)   |

## Electrical properties

|                                |          |
|--------------------------------|----------|
| Contact resistance             | ≤ 5 mΩ   |
| Insulation resistance          | ≥ 100 MΩ |
| Nominal voltage U <sub>N</sub> | 48 V AC  |
|                                | 60 V DC  |
| Nominal current I <sub>N</sub> | 1.75 A   |
| Transmission speed             | 100 Mbps |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |        |
|-------------------|--------|
| Head design       | Plug   |
| Head cable outlet | angled |
| Head thread type  | M12    |
| Coding            | D      |

## Cable/line

|                      |  |
|----------------------|--|
| Signal type/category | Ethernet CAT5 (based on IEC 11801), 100 Mbps |
|----------------------|--|

## Environmental and real-life conditions

### Ambient conditions

|                      |      |
|----------------------|------|
| Degree of protection | IP67 |
|----------------------|------|

# SACC-M12MRD-4Q SH - Data connector



1553624

<https://www.phoenixcontact.com/us/products/1553624>

|   |                  |
|---|------------------|
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C |
|---|------------------|

## Standards and regulations

M12

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | M12 connector                |
| Standards/specifications | according to IEC 61076-2-101 |


# SACC-M12MRD-4Q SH - Data connector

1553624

<https://www.phoenixcontact.com/us/products/1553624>

## Drawings

Dimensional drawing



M12 x 1 male plug, angled


# SACC-M12MRD-4Q SH - Data connector

1553624

<https://www.phoenixcontact.com/us/products/1553624>



Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side

# SACC-M12MRD-4Q SH - Data connector



1553624

<https://www.phoenixcontact.com/us/products/1553624>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-M12MRD-4Q SH - Data connector



1553624

<https://www.phoenixcontact.com/us/products/1553624>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.532 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)