

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, PCB hybrid connector, application: Hybrid, series: SH, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 4+4+4+PE / 3+N+PE, CAT5, 100 Mbps, contact connection type: Pin, Wave soldering. fully assembled

Your advantages

- Reliable transmission of signals, data, and power in a single connector
- 80% faster assembly and 60% less installation space compared to litz wire assemblies
- Cost reduction due to the elimination of additional PCB connectors
- Reduction of PCB complexity and EMC risks
- Elimination of work steps with high error potential

Commercial data

Item number	1555734
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB36
Product key	ABRJBA
GTIN	4067923033863
Weight per piece (including packing)	83 g
Weight per piece (excluding packing)	81 g
Customs tariff number	85366990
Country of origin	DE

SH-8EPC5-PCB-H2-L4-S-V2 - PCB hybrid connector



1555734

<https://www.phoenixcontact.com/us/products/1555734>

Set consists of

SH-8EPC5-PCB-L4 - Contact insert

1524754

<https://www.phoenixcontact.com/us/products/1524754>



Contact insert, straight, M23, number of positions: 4+4+4+PE / 3+N+PE, contact connection type: Pin, Wave soldering, series: SH, fully assembled, only suitable for use with the M23 hybrid solder-in connector

SH-0000000H200S - Housing for circular connector

1555725

<https://www.phoenixcontact.com/us/products/1555725>



Housing for M23 Hybrid wave soldering

SH-8EPC5-PCB-H2-L4-S-V2 - PCB hybrid connector



1555734

<https://www.phoenixcontact.com/us/products/1555734>

SH-FLAT-SEAL-0,5 - Flat gasket

1692442

<https://www.phoenixcontact.com/us/products/1692442>

Sealing ring for M23 hybrid PCB



SH-NUT-M26X1 - Flat nut

1821856

<https://www.phoenixcontact.com/us/products/1821856>

Flat nut M26 x 1



SH-8EPC5-PCB-H2-L4-S-V2 - PCB hybrid connector



1555734

<https://www.phoenixcontact.com/us/products/1555734>

SH-00000-PCB-EXTENDER - Assembly clip

1555726

<https://www.phoenixcontact.com/us/products/1555726>

Extender to ensure air clearances and creepage distances, only suitable for use in M23 Hybrid



Technical data

Notes

Safety note

Safety note

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- **WARNING:** Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.

- **WARNING:** Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

- The products are suitable for applications in plant, controller, and electrical device engineering.

- When operating the connectors in outdoor applications, they must be separately protected against environmental influences.

- Assembled products may not be manipulated or improperly opened.

- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).

- When using the product in direct connection with third-party manufacturers, the user is responsible.

- For operating voltages > 50 V AC, conductive connector housings must be grounded

- Ensure that the protective or functional ground has been properly connected.

- VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector

- Only use tools recommended by Phoenix Contact

- The installation notes/Design In documents online on the download page at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) must be observed for this product.

- Operate the connector only when it is fully plugged in and interlocked.

- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.

- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

SH-8EPC5-PCB-H2-L4-S-V2 - PCB hybrid connector



1555734

<https://www.phoenixcontact.com/us/products/1555734>

Product properties

Product type	Circular connectors (device side)
Series	SH
Thread type	M23

Electrical properties

Transmission speed	100 Mbps
--------------------	----------

Connector

Insulating body

Protection against electric shock	IEC 61984 and VDE 0623
Material (Insulating body)	PA
Material (Contact)	CuZn
Material (Contact surface)	Au
Flammability rating according to UL 94	V0
Insertion/withdrawal cycles	100
Connection method	Wave soldering
Contact switching type	Pin
Application	Hybrid
Number of positions	13
Connection profile	4+4+4+PE / 3+N+PE
Installation height	2000 m (4000 m at 300 V system voltage in accordance with DIN EN 60664-1)
Number (Power contacts)	5
Diameter (External cable diameter / Power contacts)	max. 4.15 mm
Contact diameter (Power contacts)	2 mm
Rated current Contact (Power contacts)	30 A (for max. connection cross section)
Rated voltage Contact (Power contacts)	630 V AC (Overvoltage category III/3)
	800 V DC (Overvoltage category II/3)
Rated surge voltage	6 kV
Overvoltage category	III
Degree of pollution	3
Number (Data contacts)	4
Diameter (External cable diameter / Data contacts)	max. 1.55 mm
Contact diameter (Data contacts)	0.8 mm
Rated current Contact (Data contacts)	3.6 A (for max. connection cross section)
Rated voltage Contact (Data contacts)	50 V (Contact 5 ... 8)
Rated surge voltage	1.5 kV
Overvoltage category	II, III
Degree of pollution	3
Number (Signal contacts)	4
Contact diameter (Signal contacts)	1 mm
Rated current Contact (Signal contacts)	8 A (for max. connection cross section)

SH-8EPC5-PCB-H2-L4-S-V2 - PCB hybrid connector



1555734

<https://www.phoenixcontact.com/us/products/1555734>

Rated voltage Contact (Signal contacts)	50 V (Contact 1 ... 4)
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Order information:	only to be used with item number 1524754 or 1835953
Thread type	M23
Design	straight
Type of locking	for standard and SPEEDCON interlock
Mounting type	Rear wall/screw mounting (M26 x 1)
Assembly note	Central fastening
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Seal)	FKM


Environmental and real-life conditions

Ambient conditions


Degree of protection	IP66
	IP67
	IP68 (2 m / 24 h)
Ambient temperature (operation)	-40 °C ... 115 °C (see derating curve)

Drawings

Schematic diagram




Pin assignment of pin, CAT5




Classification wave soldering profile

Diagram



I = current strength, θ = ambient temperature, power contacts A-B: 2.5 mm², 2 x 22 A, power contacts C-D: 2.5 mm², 2 x 13 A (constant), signal contacts 1-4: 0.5 mm², 4 x 2 A (constant), data contacts 5-8: AWG22, 4 x 1 A (constant)

Diagram




I = current strength, θ = ambient temperature, power contacts A-C: 2.5 mm², 3 x 26 A, signal contacts 1-4: 0.5 mm², 4 x 2 A (constant), data contacts 5-8: AWG22, 4 x 1 A (constant)

1555734

<https://www.phoenixcontact.com/us/products/1555734>

Diagram



I = current strength, ϑ = ambient temperature, power contacts A-D: 2.5 mm², 4 x 20 A, signal contacts 1-4: 0.5 mm², 4 x 2 A (constant), data contacts 5-8: AWG22, 4 x 1 A (constant)

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1555734>

 cULus Recognized Approval ID: E468743				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
Power	600 V	16 A	-	-
Signal	50 V	4 A	-	-
Data	30 V	1 A	-	-

SH-8EPC5-PCB-H2-L4-S-V2 - PCB hybrid connector



1555734

<https://www.phoenixcontact.com/us/products/1555734>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%