

FL SWITCH EP6404-4GSFP-W256-HV - Industrial Ethernet Switch



1559223

<https://www.phoenixcontact.com/us/products/1559223>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Managed switch with four RJ45 ports at 10/100/1000 Mbps, four SFP ports at 100/1000 Mbps, co-processor with E3940 Intel Atom® with 8 GB of RAM, Windows® 11 Pro operating system and operating temperature of -40 ... +70°C, 24 V DC (nominal) power supply

Product description

Developed according to IEC 61850-3 (Ambient conditions)

Your advantages

- Network structure according to IEC 61850
- IEEE 1613
- Layer 2 and Layer 3 functions
- IEEE 1588 v2 precision timing support
- Support for Access Control Lists (ACL) for traffic filtering, RADIUS, and TACAC's authentication.

Commercial data

Item number	1559223
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN36
Product key	DNN512
GTIN	4067923039179
Weight per piece (including packing)	2,738 g
Weight per piece (excluding packing)	2,074 g
Country of origin	CA

FL SWITCH EP6404-4GSFP-W256-HV - Industrial Ethernet Switch



1559223

<https://www.phoenixcontact.com/us/products/1559223>

Technical data

Dimensions

Width	82.7 mm
Height	188.39 mm
Depth	197.12 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Color (Housing)	black (RAL 9005)
Housing material	Metal

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100/1000 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)
No. of channels	4 (RJ45 ports)

Ethernet (SFP)

Connection method	SFP
Transmission speed	100/1000 Mbps (full duplex)
Transmission physics	Depending on the SFP module
No. of channels	4 (SFP ports)

Output data

Digital:

Output name	Alarm relay output: 24 V DC, 1 A maximum
-------------	--

Product properties

Product type	Switch
Product family	Managed Switch EP6000

Insulation characteristics

FL SWITCH EP6404-4GSFP-W256-HV - Industrial Ethernet Switch



1559223

<https://www.phoenixcontact.com/us/products/1559223>

Overvoltage category	II
Degree of pollution	2

Switch functions

Diagnostic functions	SysLog
Signal contact control voltage	24 V DC
Signal contact control current	1 A
Filter functions	Link Aggregation
IP parameterization	DHCP Option 82
MAC address table	16k
Management	SNMPv1/v2/v3
	Port mirroring
	SSHv2
	Telnet
	MIB support
Redundancy	RSTP
Status and diagnostic indicators	LEDs: POWER, ERROR, Link status
Time synchronization	IEEE 1588v2 (PTP)

Security functions

Authentication	RADIUS Authentication
	TACACS+ Authentication
	ACLs (Access Control Lists)

Electrical properties

Local diagnostics	Power Supply voltage Green LED
	Error Alarm signal LED red
Maximum power dissipation for nominal condition	max. 50 W
Transmission medium	Copper
	depending on the SFP module used

Supply

Supply voltage (AC/DC)	240 V AC/DC
Supply voltage range	100 V AC/DC ... 240 V AC/DC

Function

Signal contact control voltage	24 V DC
Signal contact control current	1 A

Connection data

Connection method	Screw connection
-------------------	------------------

Environmental and real-life conditions

Ambient conditions

FL SWITCH EP6404-4GSFP-W256-HV - Industrial Ethernet Switch



1559223

<https://www.phoenixcontact.com/us/products/1559223>

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Standards and regulations

Standard designation	Ambient conditions
Standards/specifications	IEC 61850-3
	IEEE 1613

Approvals

Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

EMC data

Noise immunity	IEC 61850-3, IEEE 1613, EN 61000-6-2: 2005
----------------	--

Signaling

Status display	LEDs: POWER, ERROR, Link status
----------------	---------------------------------

FL SWITCH EP6404-4GSFP-W256-HV - Industrial Ethernet Switch



1559223

<https://www.phoenixcontact.com/us/products/1559223>

Classifications

ECLASS

ECLASS-13.0	19170401
ECLASS-15.0	19170401

ETIM

ETIM 10.0	EC000734
-----------	----------

FL SWITCH EP6404-4GSFP-W256-HV - Industrial Ethernet Switch



1559223

<https://www.phoenixcontact.com/us/products/1559223>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I, 7(c)-II

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	1-Methyl-2-pyrrolidone (NMP)(CAS: 872-50-4)
	N,N-dimethylacetamide(CAS: 127-19-5)
	1, 2-dimethoxyethane; ethylene glycol dimethyl ether (EGDME)(CAS: 110-71-4)
	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead titanium zirconium oxide(CAS: 12626-81-2)
	Lead titanium trioxide(CAS: 12060-00-3)
	4,4'-isopropylidenediphenol(CAS: 80-05-7)
	Terphenyl, hydrogenated(CAS: 61788-32-7)
	Lead(CAS: 7439-92-1)
	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one(CAS: 71868-10-5)

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com