

TCP 5A - Thermal device circuit breaker



1538622

<https://www.phoenixcontact.com/us/products/1538622>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



1-channel thermal device circuit breaker for protecting loads at 250 V AC / 72 V DC in the event of an overload. For installation on fuse terminal blocks and interfaces for flat plug-in fuse of type C according to standard ISO 8820-3. With fixed nominal current: 5 A

Your advantages

- Fast, replacement part-free recommissioning after an event with the reconnection options
- Easy to retrofit in existing systems with vehicle flat-type fuses with identical pin connector pattern
- System disconnection for maintenance actions via the integrated device switch

Commercial data

Item number	1538622
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	CL15
Product key	CLA111
GTIN	4067923010086
Weight per piece (including packing)	11.45 g
Weight per piece (excluding packing)	16.742 g
Customs tariff number	85362010
Country of origin	ID

TCP 5A - Thermal device circuit breaker



1538622

<https://www.phoenixcontact.com/us/products/1538622>

Technical data

Notes

General	When mounted in rows, the nominal device current can be limited to just 80% or must be overdimensioned accordingly.
---------	---

Product properties

Product type	Thermal device circuit breakers
Type	Male
Number of positions	1
No. of channels	1

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Electrical properties

Fuse type	Automatic device
Maximum power dissipation for nominal condition	≤ 0.9 VA
Fuse	Slow-blow

General

Rated voltage	250 V AC
	65 V DC
	250 V AC (AC according to UL 1077)
	72 V DC (DC according to UL 1077)
Rated current I_N	5 A
Rated surge voltage	2.5 kV
Insulation resistance R_{ISO}	> 100 M Ω (500 V DC)
Tripping method	T (thermal)
Device resistance	0.05 Ω
Rated short-circuit switching capacity I_{cn}	30 A (250 V AC / 65 V DC)
	50 A (30 V DC)
Short-circuit switching capacity	2000 A (250 V AC / UL 1077)
	2000 A (72 V DC / UL 1077)
Dielectric strength	3000 V AC (Actuation area)
	1500 V AC (Installation area)
Switching cycles, max.	6000 (At $1 \times I_n$, low-induction)
	3000 (At $1 \times I_n$, inductive)
	500 (At $2 \times I_n$, inductive)
Contact switching type	Type C in accordance with ISO 8820-3

Connection data

Nominal current	5 A
Nominal voltage	250 V AC

TCP 5A - Thermal device circuit breaker




1538622

<https://www.phoenixcontact.com/us/products/1538622>

	65 V DC
Connection method	pluggable

Dimensions

Dimensional drawing	
Width	8.2 mm
Height	24.4 mm
Depth	44.5 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V-0
Insulating material group	IIIb
Insulating material	PPS

Mechanical properties

Mechanical data	
Open side panel	No

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP40 (Actuation area)
Ambient temperature (operation)	-20 °C ... 60 °C
Altitude	≤ 4000 m (amsl)
Humidity test	240 h, 95 % RH, 40 °C

Mounting

Mounting type	on base element
---------------	-----------------

TCP 5A - Thermal device circuit breaker

1538622

<https://www.phoenixcontact.com/us/products/1538622>



Drawings

Dimensional drawing



TCP 5A - Thermal device circuit breaker

1538622

<https://www.phoenixcontact.com/us/products/1538622>



Dimensional drawing



TCP 5A - Thermal device circuit breaker

1538622

<https://www.phoenixcontact.com/us/products/1538622>



Product drawing




The figure shows the product with the base element PT 6-FSI/C-LED 24 (Item No.: 3212172).

TCP 5A - Thermal device circuit breaker

1538622

<https://www.phoenixcontact.com/us/products/1538622>

Application drawing



Fuse terminal blocks in interconnected arrangement,
block consisting of 5 fuse terminal blocks

TCP 5A - Thermal device circuit breaker

1538622

<https://www.phoenixcontact.com/us/products/1538622>

Application drawing




Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks

TCP 5A - Thermal device circuit breaker


1538622

<https://www.phoenixcontact.com/us/products/1538622>

Application drawing



Application drawing



Diagram



Trigger characteristic

TCP 5A - Thermal device circuit breaker



1538622

<https://www.phoenixcontact.com/us/products/1538622>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1538622>



cUL Recognized

Approval ID: FILE E 140459



UL Recognized

Approval ID: FILE E 140459



VDE approval of drawings

Approval ID: 40034332



CCC

Approval ID: 2025010307749780

TCP 5A - Thermal device circuit breaker



1538622

<https://www.phoenixcontact.com/us/products/1538622>

Classifications

ECLASS

ECLASS-13.0	27140401
ECLASS-15.0	27140401

ETIM

ETIM 10.0	EC003538
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

TCP 5A - Thermal device circuit breaker



1538622

<https://www.phoenixcontact.com/us/products/1538622>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com