

VS-04-2X2X26C7/7-SDA/SDA/3,5 - USB cable



1563151

<https://www.phoenixcontact.com/us/products/1563151>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled USB cable, shielded, color: RAL 5021 (water blue), PUR outer sheath, USB type A/standard on USB type A/standard, length: 3.5 m

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1563151 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB14 |
| Product key | ABNDBA |
| GTIN | 4046356302531 |
| Weight per piece (including packing) | 229.5 g |
| Weight per piece (excluding packing) | 192.5 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

1563151

<https://www.phoenixcontact.com/us/products/1563151>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Sensor type | USB 2.0 |
| Number of positions | 4 |
| Shielded | yes |

Insulation characteristics

| | |
|---------------------|---|
| Degree of pollution | 2 |
|---------------------|---|

Electrical properties

| | |
|---|---------|
| Rated voltage (III/3) | 125 V |
| Rated current | 1 A |
| Transmission medium | Copper |
| Transmission characteristics (category) | USB 2.0 |
| Wave impedance | 100 Ω |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

Material specifications

| | |
|------------------------|--------------------|
| Housing material | PA |
| Outer sheath, material | PUR |
| Conductor material | Bare Cu litz wires |

Cable/line

FireWire [980]

| | |
|-------------------------------------|--|
| Cable weight | 59 kg/km |
| Number of positions | 6 |
| Shielded | yes |
| Cable type | FireWire [980] |
| Conductor structure | 2x2xAWG26/7 + 2xAWG20/19, S/FTP |
| Signal runtime | 4.6 ns/m |
| Signal speed | 0.72 c |
| Conductor structure signal line | 7x 0.15 mm |
| AWG signal line | 26 |
| Conductor structure, voltage supply | 19x 0.20 mm |
| AWG power supply | 20 |
| Conductor cross-section | 2x 2x 0.14 mm ² (Signal line) |
| | 2x 0.5 mm ² (Power supply) |
| Wire diameter incl. insulation | ≤ 1.05 mm (Signal line) |

VS-04-2X2X26C7/7-SDA/SDA/3,5 - USB cable




1563151

<https://www.phoenixcontact.com/us/products/1563151>

| | |
|---|---|
| | nom. 1.4 mm (Power supply) |
| External cable diameter | 6.70 mm |
| Outer sheath, material | PUR |
| External sheath, color | water blue RAL 5021 |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | Cell PE (Signal line) |
| | PVC (Power supply) |
| Single wire, color | white-blue, white-orange, white, black |
| Twisted pairs | 2 cores to the pair |
| Type of pair shielding | Aluminum-lined polyester foil |
| Overall twist | Two pairs and two power supply wires to the core |
| Max. conductor resistance | 150 Ω/km |
| Insulation resistance | 5 GΩ*km |
| Coupling resistance | 5.00 mΩ/m (at 10 MHz) |
| Wave impedance | 100 Ω ±5 % (at 100 MHz) |
| Working capacitance | 42 pF (per meter) |
| Nominal voltage, cable | ≤ 125 V |
| Test voltage | 1000 V |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 5 x D |
| Smallest bending radius, fixed installation | 34 mm |
| Smallest bending radius, movable installation | 34 mm |
| Tensile strength | ≤ 30 N |
| Shield attenuation | 60.00 dB (up to 1000 MHz) |
| Flame resistance | complying with IEC 60332-2-2 |
| Resistance to oil | in accordance with EN 60811-2-1 |
| Other resistance | Microbe resistance as per DIN VDE 0282 |
| | Hydrolysis resistance as per DIN 53504 |
| Special properties | Free of substances which would hinder coating with paint or varnish |
| Ambient temperature (operation) | -40 °C ... 70 °C (cable, fixed installation) |
| | -10 °C ... 50 °C (Cable, flexible installation) |

Drawings

Dimensional drawing



USB connector, type A, Standard


VS-04-2X2X26C7/7-SDA/SDA/3,5 - USB cable

1563151

<https://www.phoenixcontact.com/us/products/1563151>



Dimensional drawing




USB connector, type A, Standard

1563151


<https://www.phoenixcontact.com/us/products/1563151>

Schematic diagram



Pin assignment plug USB, type A

Schematic diagram




Pin assignment plug USB, type A

1563151

<https://www.phoenixcontact.com/us/products/1563151>

Circuit diagram



VS-04-2X2X26C7/7-SDA/SDA/3,5 - USB cable



1563151

<https://www.phoenixcontact.com/us/products/1563151>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060328 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

VS-04-2X2X26C7/7-SDA/SDA/3,5 - USB cable



1563151

<https://www.phoenixcontact.com/us/products/1563151>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com