

# SACC-DSIV-FS-5CON-L180 SCO - Device connector rear mounting



1542570

<https://www.phoenixcontact.com/us/products/1542570>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Socket, straight, M12-SPEEDCON, A-coding, Wave soldering

## Commercial data

Item number	1542570
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB26
Product key	ABQEHI
GTIN	4046356097864
Weight per piece (including packing)	12.67 g
Weight per piece (excluding packing)	9.879 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSIV-FS-5CON-L180 SCO - Device connector rear mounting



1542570

<https://www.phoenixcontact.com/us/products/1542570>

## Technical data

### Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

### Mounting

Mounting type	Rear mounting
---------------	---------------

### Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	no
Coding	A
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	Cu alloy
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	HB

### Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	60 V
Nominal current $I_N$	4 A

### Connection data

#### Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

### Connector

#### Connection 1

Head design	Socket
-------------	--------

# SACC-DSIV-FS-5CON-L180 SCO - Device connector rear mounting



1542570

<https://www.phoenixcontact.com/us/products/1542570>

Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

# SACC-DSIV-FS-5CON-L180 SCO - Device connector rear mounting

1542570

<https://www.phoenixcontact.com/us/products/1542570>

## Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

# SACC-DSIV-FS-5CON-L180 SCO - Device connector rear mounting



1542570

<https://www.phoenixcontact.com/us/products/1542570>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 9.0	EC003568
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSIV-FS-5CON-L180 SCO - Device connector rear mounting



1542570

<https://www.phoenixcontact.com/us/products/1542570>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	97df846c-d77c-420b-9bbb-ef482d96a582

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)