

# SACC-FS-5CON-PG 7-M SCO - Connector



1543032

<https://www.phoenixcontact.com/us/products/1543032>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 5-position, Socket straight M12 SPEEDCON, coding: A, Screw connection, knurl material: Brass, nickel-plated, cable gland Pg7, external cable diameter 4 mm .. 6 mm

## Your advantages

- Safe use in the field, thanks to a high degree of protection
- Save time, thanks to installation with SPEEDCON fast locking system
- Screw connection: proven connection technology for a large selection of different conductors

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1543032       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF30          |
| Product key                          | AF2CAA        |
| GTIN                                 | 4046356097604 |
| Weight per piece (including packing) | 26.7 g        |
| Weight per piece (excluding packing) | 25.9 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SACC-FS-5CON-PG 7-M SCO - Connector



1543032

<https://www.phoenixcontact.com/us/products/1543032>

## Technical data

### Notes

|               |   |
|---------------|---|
| Assembly note | <b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|---|


### Product properties

|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Number of positions  | 5                               |
| No. of cable outlets | 1                               |
| Shielded             | no                              |
| Coding               | A                               |
| Cable outlet         | straight                        |
| Pg screw connection  | Pg7                             |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Length              | 54 mm  |

### External dimensions

|                  |               |
|------------------|---------------|
| Outside diameter | 4 mm ... 6 mm |
|------------------|---------------|

### Housing

|                  |       |
|------------------|-------|
| Diameter housing | 20 mm |
|------------------|-------|

### Material specifications

|  |                      |
|--|----------------------|
| Flammability rating according to UL 94 | HB                   |
| Seal material                          | NBR                  |
| Material of grip body                  | PBT                  |
| Contact material                       | CuZn                 |
| Contact surface material               | CuSnZn               |
| Contact carrier material               | PA                   |
| Material for screw connection          | Brass, nickel-plated |

### Connection data

# SACC-FS-5CON-PG 7-M SCO - Connector



1543032

<https://www.phoenixcontact.com/us/products/1543032>

## Conductor connection

|   |   |
|---|---|
| Connection method                       | Screw connection  |
| Connection cross section                | 0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (without ferrule) |
|   | 0.14 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (with ferrule)    |
|   | 0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (solid)           |
| Connection cross section AWG            | 24 ... 18 (without ferrule)                                     |
|   | 26 ... 20 (with ferrule)  |
| Stripping length of the individual wire | 5 mm  |
| Tightening torque                       | 0.4 Nm (M12 knurl)  |
|   | 0.2 Nm (Screw terminal blocks)                                  |
|   | 0.8 Nm ... 1 Nm (Pressure screw with sleeve housing)            |

## Electrical properties

|                                |          |
|--------------------------------|----------|
| Rated surge voltage            | 1.5 kV   |
| Contact resistance             | ≤ 8 mΩ   |
| Insulation resistance          | ≥ 100 MΩ |
| Nominal voltage U <sub>N</sub> | 48 V AC  |
|                                | 60 V DC  |
| Nominal current I <sub>N</sub> | 4 A      |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Socket   |
| Head cable outlet | straight |
| Head thread type  | M12      |
| Head locking type | SPEEDCON |
| Coding            | A        |

## Cable/line

|   |           |
|---|-----------|
| Signal type/category                    | Universal |
| Stripping length of the individual wire | 5 mm      |

## Environmental and real-life conditions

### Ambient conditions

|   |                                  |
|---|----------------------------------|
| Degree of protection  | IP67                             |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C (Plug / socket) |

## Standards and regulations

# SACC-FS-5CON-PG 7-M SCO - Connector



1543032

<https://www.phoenixcontact.com/us/products/1543032>

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |

# SACC-FS-5CON-PG 7-M SCO - Connector

1543032

<https://www.phoenixcontact.com/us/products/1543032>


## Drawings

Dimensional drawing



M12 x 1 socket, straight

Schematic diagram



Male/Female M12

1543032

<https://www.phoenixcontact.com/us/products/1543032>

Schematic diagram



Cable connection side M12 (screw connection)

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

# SACC-FS-5CON-PG 7-M SCO - Connector



1543032

<https://www.phoenixcontact.com/us/products/1543032>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

1543032

<https://www.phoenixcontact.com/us/products/1543032>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |  |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Imidazolidine-2-thione (2-imidazoline-2-thiol)(CAS: 96-45-7) |
|                                     | Lead(CAS: 7439-92-1)   |
| SCIP                                | 79fe8518-f367-4da9-a96e-d0f67fb2f6ae                         |

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.844 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)