

BPC 120 FT S 16-25 OG - Connector



1571066

<https://www.phoenixcontact.com/us/products/1571066>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Range of articles: BPC 120, color: orange, number of positions: 1, min. conductor cross-section: 16 mm², max. conductor cross-section: 25 mm², rated voltage: 1500 V DC, rated current: 120 A, Connection method: Thread connection

Your advantages

- Patented design, with 3 proofs and one rotation
- Safety lock
- 360° free rotation and flexible wiring
- Foolproof mechanism installed
- Touch-proof
- Mismatching and short circuit proof

Commercial data

Item number	1571066
Packing unit	15 pc
Minimum order quantity	15 pc
Sales key	AB04
Product key	ABLDBA
GTIN	4067923057777
Weight per piece (including packing)	28.52 g
Weight per piece (excluding packing)	23.2 g
Customs tariff number	85359000
Country of origin	CN

Technical data

Notes

Safety note

Safety note

- **WARNING:** Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
- **WARNING:** Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
- WARNING:** The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.
- The products are suitable for applications in plant, controller, and electrical device engineering.
- Assembled products may not be manipulated or improperly opened.
- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).
- When using the product in direct connection with third-party manufacturers, the user is responsible.
- For operating voltages > 50 V AC, conductive connector housings must be grounded
- Ensure that the protective or functional ground has been properly connected.
- Observe the corresponding technical data. You will find information:
 - o On the product
 - o On the packing label
 - o In the supplied documentation
 - o Online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) under the product
- The installation notes/Design In documents online on the download page at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) must be observed for this product.
- Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
- Operate the connector only when it is fully plugged in and interlocked.
- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

BPC 120 FT S 16-25 OG - Connector



1571066

<https://www.phoenixcontact.com/us/products/1571066>

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.

Product properties

Product type	Connectors for energy storage
Product family	BPC 120
Number of positions	1

Insulation characteristics

Degree of pollution	2
---------------------	---

Electrical properties

Rated voltage (III/2)	1500 V DC
Rated voltage	1500 V DC (III/2.00)
	1000 V AC (III/2.00)
Rated current	120 A (with 25 mm ² conductor cross-section, in accordance with IEC 61984)
	76 A (with 16 mm ² conductor cross-section, in accordance with IEC 61984)
Contact resistance	≤ 0.5 mΩ
Nominal voltage U _N	1500 V

Connection data

Connection method	Thread connection
Tightening torque	... 1 Nm

Material specifications

Color	orange
Material Housing	Polyamide
Material Contact	Copper alloy
Material Seal	Rubber
Flammability rating according to UL 94	V0
Insulating material	PA
Contact surface material	Ni/Ag

Cable/line

Single wire, cross section	16 mm ² 25 mm ²
Halogen-free	yes

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
Insertion force	≤ 75 N
Withdrawal force	≥ 10 N

Environmental and real-life conditions

BPC 120 FT S 16-25 OG - Connector



1571066

<https://www.phoenixcontact.com/us/products/1571066>

Ambient conditions

Degree of protection	IP65/IP67 (Mating plug)
Ambient temperature (operation)	-40 °C ... 125 °C (incl. temperature increase)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	4000 m

Standards and regulations

Standard designation	TÜV (PPP 51090B)
Standards/specifications	UL 4128

BPC 120 FT S 16-25 OG - Connector



1571066

<https://www.phoenixcontact.com/us/products/1571066>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1571066>

 UL Recognized Approval ID: E511681 V1S4				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	1500 V	120 A	- 4	-

 TÜV SÜD Type tested Approval ID: 704072474902 02				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	1500 V	120 A	-	16 - 25

BPC 120 FT S 16-25 OG - Connector



1571066

<https://www.phoenixcontact.com/us/products/1571066>

Classifications

ECLASS

ECLASS-13.0	27440209
ECLASS-15.0	27440209

ETIM

ETIM 10.0	EC002641
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

BPC 120 FT S 16-25 OG - Connector



1571066

<https://www.phoenixcontact.com/us/products/1571066>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com