


# SAC-5P-M12MS/ 2,0-500 SH AE KA - Sensor/actuator cable



1571693

<https://www.phoenixcontact.com/us/products/1571693>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PVC, black RAL 9005, shielded, Plug straight M12, coding: A, on free cable end, cable length: 2 m

## Commercial data

Item number	1571693
Packing unit	5 pc
Minimum order quantity	25 pc
Product key	AF1CKA
GTIN	4046356364942
Weight per piece (including packing)	140.48 g
Weight per piece (excluding packing)	140.48 g
Country of origin	PL

# SAC-5P-M12MS/ 2,0-500 SH AE KA - Sensor/actuator cable



1571693

<https://www.phoenixcontact.com/us/products/1571693>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	5
No. of cable outlets	1
Shielded	yes
Coding	A

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

### Electrical properties

Insulation resistance	≥ 100 MΩ
Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	4 A

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

### Signaling

Status display	no
Status display present	no

### Connector

#### Connection 1

Type	Plug straight M12
Number of positions	5
Coding type	A

#### Connection 2

Type	free cable end
------	----------------


# SAC-5P-M12MS/ 2,0-500 SH AE KA - Sensor/actuator cable



1571693

<https://www.phoenixcontact.com/us/products/1571693>

## Cable/line

Cable length	2 m
PVC black [PVC]	
Dimensional drawing	
Cable weight	55 kg/km
Number of positions	5
Shielded	yes
Cable type	PVC black [PVC]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	5x 0.34 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.35 mm ±0.02 mm
External cable diameter	5.90 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material, filler	PVC
Material wire insulation	PVC
Single wire, color	brown, white, blue, black, gray
Thickness, insulation	≥ 0.23 mm (Core insulation) ≥ 0.76 mm (Outer cable sheath)
Overall twist	5 wires around filler to the core
Optical shield covering	85 %
Max. conductor resistance	≤ 58 Ω/km (at 20 °C)
Insulation resistance	≥ 10 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	59 mm
Flame resistance	As per UL-Style 2464
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

# SAC-5P-M12MS/ 2,0-500 SH AE KA - Sensor/actuator cable



1571693

<https://www.phoenixcontact.com/us/products/1571693>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

# SAC-5P-M12MS/ 2,0-500 SH AE KA - Sensor/actuator cable

1571693

<https://www.phoenixcontact.com/us/products/1571693>

## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side


# SAC-5P-M12MS/ 2,0-500 SH AE KA - Sensor/actuator cable



1571693

<https://www.phoenixcontact.com/us/products/1571693>

Diagram



# SAC-5P-M12MS/ 2,0-500 SH AE KA - Sensor/actuator cable



1571693

<https://www.phoenixcontact.com/us/products/1571693>

Circuit diagram



Contact assignment of the M12 plug

# SAC-5P-M12MS/ 2,0-500 SH AE KA - Sensor/actuator cable



1571693

<https://www.phoenixcontact.com/us/products/1571693>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

# SAC-5P-M12MS/ 2,0-500 SH AE KA - Sensor/actuator cable



1571693

<https://www.phoenixcontact.com/us/products/1571693>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)