

# SAC-5P-MS/ 2,5-927/FR SCO JLG - Sensor/actuator cable



1573701

<https://www.phoenixcontact.com/us/products/1573701>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, PVC, black, Plug straight M12 SPEEDCON, coding: A, on Socket angled M12 SPEEDCON

## Commercial data

Item number	1573701
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF04
Product key	AF1CDD
GTIN	4046356435956
Weight per piece (including packing)	255.1 g
Weight per piece (excluding packing)	255.1 g
Customs tariff number	85444290
Country of origin	PL

# SAC-5P-MS/ 2,5-927/FR SCO JLG - Sensor/actuator cable



1573701

<https://www.phoenixcontact.com/us/products/1573701>

## Technical data

### Product properties

Product type	Data cable preassembled
--------------	-------------------------

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC

### Connector

#### Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	5
Locking type	SPEEDCON
Coding type	A (Standard)

#### Connection 2

Type	Socket angled M12 SPEEDCON
Number of positions	5
Locking type	SPEEDCON

### Cable/line

#### CANopen®/DeviceNet™, PVC, black [927]

Cable weight	83 kg/km
UL AWM Style	2464 (80°C/300 V)
Number of positions	4
Shielded	yes
Cable type	CANopen®/DeviceNet™, PVC, black [927]
Signal runtime	4.46 ns/m
Conductor structure signal line	44x 0.10 mm
AWG signal line	22
Conductor structure, voltage supply	44x 0.10 mm
AWG power supply	22
Conductor cross-section	2x 0.34 mm <sup>2</sup> (Signal line)
	2x 0.34 mm <sup>2</sup> (Power supply)
	1x 0.38 mm <sup>2</sup> (Drain wire)
Wire diameter incl. insulation	2.55 mm (Signal line)
	1.37 mm (Power supply)
External cable diameter	8.30 mm ±0.3 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Tin-plated Cu litz wires
Material wire insulation	Foamed PP (Signal line)

# SAC-5P-MS/ 2,5-927/FR SCO JLG - Sensor/actuator cable



1573701

<https://www.phoenixcontact.com/us/products/1573701>

	PVC (Power supply)
Single wire, color	red-black, blue-white
Thickness, insulation	≥ 0.30 mm (Wire insulation power supply)
Thickness, outer sheath	≥ 1.00 mm
Twisted pairs	2 cores to the pair
Type of pair shielding	Aluminum-lined polyester foil
Overall twist	2 pairs with filler elements, around a drain wire in the center to the core
Optical shield covering	85 %
Max. conductor resistance	≤ 56 Ω/km
Insulation resistance	≥ 20 MΩ*km
Wave impedance	120 Ω ±12 Ω (f = 1 MHz)
Working capacitance	approx. 39.8 nF (Signal line, line-line)
	≤ 4000 pF (Signal line, line-shield)
Nominal voltage, cable	≤ 300 V
Test voltage	2000 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, fixed installation	34 mm
Smallest bending radius, movable installation	67 mm
Flame resistance	in acc. with UL 1581, section 1061
Ambient temperature (operation)	-30 °C ... 80 °C

# SAC-5P-MS/ 2,5-927/FR SCO JLG - Sensor/actuator cable



1573701

<https://www.phoenixcontact.com/us/products/1573701>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### UNSPSC

UNSPSC 21.0	26121604
-------------	----------

# SAC-5P-MS/ 2,5-927/FR SCO JLG - Sensor/actuator cable



1573701

<https://www.phoenixcontact.com/us/products/1573701>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)