



PTS 0,5/ 2-PH-5,75 BKRD KNX - PCB connector



1574300

<https://www.phoenixcontact.com/us/products/1574300>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB connector, nominal cross section: 0.5 mm², color: multicolored, nominal current: 6 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Socket, number of rows: 1, number of positions: 2, product range: PTS 0,5/..-PH, pitch: 5.75 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON PST 1,0, locking: without, mounting method: without, type of packaging: packed in cardboard

Your advantages

- Time saving push-in connection, tools not required
- Defined contact force ensures that contact remains stable over the long term
- Quick and convenient testing using integrated test option
- Potentials can be easily looped through – ideal for BUS applications
- Small component size for applications where space is at a premium

Commercial data

Item number	1574300
Packing unit	250 pc
Minimum order quantity	250 pc
Sales key	AA02
Product key	AAAFHA
GTIN	4067923062979
Weight per piece (including packing)	1.86 g
Weight per piece (excluding packing)	0.217 g
Customs tariff number	85366990
Country of origin	CN

PTS 0,5/ 2-PH-5,75 BKRD KNX - PCB connector



1574300

<https://www.phoenixcontact.com/us/products/1574300>

Technical data

Product properties

Product type	PCB connector
Product family	PTS 0,5/..-PH
Product line	COMBICON Connectors XS
Number of positions	2
Pitch	5.75 mm
Number of rows	1

Electrical properties

Properties

Nominal current I_N	6 A
Nominal voltage U_N	320 V
Contact resistance	1.4 mΩ
Rated voltage (III/3)	250 V
Rated surge voltage (III/3)	4 kV
Rated voltage (III/2)	320 V
Rated surge voltage (III/2)	4 kV
Rated voltage (II/2)	400 V
Rated surge voltage (II/2)	4 kV

Data transmission

Signal type	KNX
Transmission medium	Copper
Data transmission rate	9.6 kbps

Connection data

Interlock

Locking type	without
Mounting type	without

Conductor connection

Connection method	Push-in spring connection
Conductor/PCB connection direction	0 °
Conductor cross-section rigid	0.34 mm² ... 0.75 mm²
Cylindrical gauge a x b / diameter	- / 1.0 mm
Stripping length	5 mm

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
------	--

PTS 0,5/ 2-PH-5,75 BKRD KNX - PCB connector



1574300


<https://www.phoenixcontact.com/us/products/1574300>

Contact material	Cu alloy
Surface characteristics	tin-plated
Metal surface terminal point (top layer)	Tin (- 2 µm Sn)
Metal surface terminal point (middle layer)	Nickel (- 0.76 µm Ni)
Metal surface contact area (top layer)	Tin (- 2 µm Sn)
Metal surface contact area (middle layer)	Nickel (- 0.76 µm Ni)

Material data - housing

Color (Housing)	multicolored (-)
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0

Dimensions

Dimensional drawing	
Pitch	5.75 mm
Width [w]	12.45 mm
Height [h]	10 mm
Length [l]	10 mm

Mechanical tests

Conductor connection

Specification	IEC 60999-1:1999-11
Result	Test passed

Test for conductor damage and slackening

Specification	IEC 60999-1:1999-11
Result	Test passed

Repeated connection and disconnection

Specification	IEC 60999-1:1999-11
Result	Test passed

Pull-out test

Specification	IEC 60999-1:1999-11
Conductor cross-section/conductor type/tractive force setpoint/actual value	0.34 mm² / solid / > 15 N
	0.75 mm² / solid / > 30 N

Resistance of inscriptions

Specification	IEC 60068-2-70:1995-12
---------------	------------------------

PTS 0,5/ 2-PH-5,75 BKRD KNX - PCB connector



1574300

<https://www.phoenixcontact.com/us/products/1574300>

Result	Test passed
--------	-------------

Visual inspection

Specification	IEC 60512-1-1:2002-02
Result	Test passed

Dimension check

Specification	IEC 60512-1-2:2002-02
Result	Test passed

Environmental and real-life conditions

Durability test

Specification	IEC 60512-9-1:2010-03
Impulse withstand voltage at sea level	4.8 kV
Contact resistance R_1	1.4 mΩ
Contact resistance R_2	1.6 mΩ
Insertion/withdrawal cycles	25
Insulation resistance, neighboring positions	> 5 MΩ

Climatic test

Specification	EN ISO 22479:2022-06
Corrosive stress	0.2 dm ³ SO ₂ on 300 dm ³ /40 °C/1 cycle
Thermal stress	100 °C/168 h
Power-frequency withstand voltage	2.21 kV

Glow-wire test

Specification	IEC 60695-2-11:2021-10
Temperature	850 °C
Time of exposure	30 s

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-60 °C ... 100 °C (dependent on the derating curve)

Electrical tests

Thermal test | Test group C

Specification	IEC 60512-5-1:2002-02
Tested number of positions	2

Insulation resistance

Specification	IEC 60512-3-1:2002-02
Insulation resistance, neighboring positions	> 5 MΩ

Air clearances and creepage distances |

PTS 0,5/ 2-PH-5,75 BKRD KNX - PCB connector



1574300


<https://www.phoenixcontact.com/us/products/1574300>

Specification	IEC 60664-1:2020-05
Insulating material group	I
Comparative tracking index (IEC 60112)	CTI 600
Rated insulation voltage (III/3)	250 V
Rated surge voltage (III/3)	4 kV
minimum clearance value - non-homogenous field (III/3)	3 mm
minimum creepage distance (III/3)	3.2 mm
Rated insulation voltage (III/2)	320 V
Rated surge voltage (III/2)	4 kV
minimum clearance value - non-homogenous field (III/2)	3 mm
minimum creepage distance (III/2)	3 mm
Rated insulation voltage (II/2)	400 V
Rated surge voltage (II/2)	4 kV
minimum clearance value - non-homogenous field (II/2)	3 mm
minimum creepage distance (II/2)	3 mm

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

Drawings



Type: PTS 0,5/...-PH-5,75 with PST 1,0/...-5,75

PTS 0,5/ 2-PH-5,75 BKRD KNX - PCB connector



1574300

<https://www.phoenixcontact.com/us/products/1574300>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1574300>

 VDE Zeichengenehmigung Approval ID: 40058359				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	320 V	6 A	-	0.34 - 0.75

 cULus Recognized Approval ID: E60425-20250418				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	150 V	7 A	18 - 22	-
C				
	150 V	7 A	18 - 22	-

PTS 0,5/ 2-PH-5,75 BKRD KNX - PCB connector



1574300

<https://www.phoenixcontact.com/us/products/1574300>

Classifications

ECLASS

ECLASS-13.0	27460202
ECLASS-15.0	27460202

ETIM

ETIM 10.0	EC002638
-----------	----------

PTS 0,5/ 2-PH-5,75 BKRD KNX - PCB connector



1574300

<https://www.phoenixcontact.com/us/products/1574300>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com