

# SAC-4P-10,0-186/M12FS SO - Sensor/actuator cable



1548930

<https://www.phoenixcontact.com/us/products/1548930>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, PUR, black-gray RAL 7021, cable length: 10 m

## Commercial data

Item number	1548930
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF1CCA
GTIN	4046356141550
Weight per piece (including packing)	631.6 g
Weight per piece (excluding packing)	631.6 g
Customs tariff number	85444290
Country of origin	PL

# SAC-4P-10,0-186/M12FS SO - Sensor/actuator cable



1548930

<https://www.phoenixcontact.com/us/products/1548930>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Shielded	no

### Mechanical properties


#### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

### Cable/line

Cable length	10 m
--------------	------

#### PUR POWER 0.75 mm<sup>2</sup> black [186]

Dimensional drawing	
Cable weight	57 kg/km
UL AWM Style	20549 / 1061 (80°C/300 V)
Number of positions	4
Shielded	no
Cable type	PUR POWER 0.75 mm <sup>2</sup> black [186]
Conductor structure signal line	42x 0.15 mm
AWG signal line	18
Conductor cross-section	4x 0.75 mm <sup>2</sup> (power line)
Wire diameter incl. insulation	1.75 mm ±0.05 mm
External cable diameter	5.90 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation) ≥ 0.76 mm (Outer cable sheath)
Overall twist	4 wires, twisted
Max. conductor resistance	max. 26 Ω/km (at 20 °C)
Insulation resistance	≥ 1 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V

# SAC-4P-10,0-186/M12FS SO - Sensor/actuator cable



1548930

<https://www.phoenixcontact.com/us/products/1548930>

Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	59 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 59 mm, Traversing path: 5 m, Traversing rate: 3 m/s, Acceleration: 5 m/s <sup>2</sup>
Flame resistance	according to UL 758/1581 (horizontal)
	in accordance with UL 758/1581 FT2
Resistance to oil	According to DIN EN 60811-2-1, 168 h at 100°C
Other resistance	hydrolysis and microbe resistant
	Low adhesion
	abrasion-resistant
	Resistant to salt water
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

# SAC-4P-10,0-186/M12FS SO - Sensor/actuator cable



1548930

<https://www.phoenixcontact.com/us/products/1548930>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

1548930

<https://www.phoenixcontact.com/us/products/1548930>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)