

CK8,0-ED-35,00M AG - Crimp contact



1550053

<https://www.phoenixcontact.com/us/products/1550053>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: HC-M-...-35, Pin, turned, contact diameter: 8 mm, rated current: 100 A, connection cross section: 35 mm² ... 35 mm², AWG 2...2 , contact material: Cu alloy

Commercial data

Item number	1550053
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF65
Product key	AF7AIG
GTIN	4067923025646
Weight per piece (including packing)	23.4 g
Weight per piece (excluding packing)	23.4 g
Customs tariff number	85366990
Country of origin	DE

CK8,0-ED-35,00M AG - Crimp contact



1550053

<https://www.phoenixcontact.com/us/products/1550053>

Technical data

Notes

Notes on the product family	for HC-M-...-35 contact carriers
Note on application	The quality of a crimp connection is determined by DIN EN 60352-2.
Assembly note	The contacts are qualified for crimping dies in accordance with DIN 46235. Klauke, for example, offers an appropriate tool: Crimping dies from the D22 series are required for the EKM6022 battery-powered hydraulic crimping pliers. Due to the narrow crimping width of 5 mm, it is very important to make two compressions next to one another. For the EK12042 model, crimping dies from the HD13 series are required. Due to a wider crimping process, only one compression is required.
Note on application	Note on crimp connection technology: For flexible wires only. The specified conductor cross-sections refer to the nominal cross-section of the cable used. The wiring space of the crimp connection technology is designed for fine-stranded cables in accordance with VDE 0295 Class 5. Deviating cable structures (e.g., Class 1.2 and 6 or AWG cables) should be checked before use.

Product properties

Product type	Crimp contact
Series	HC-M-...-35
Contact material type	turned

Connection data

Connection technology	
Contact connection type	Pin
Connection method	Crimp connection

Conductor connection	
Stripping length	16 mm
Connection cross section	35 mm ² ... 35 mm ²
Connection cross section AWG	2 ... 2

Material specifications

Material Contact	Cu alloy (lead-free)
Material Contact surface	Ag

Dimensions

Diameter (Contact diameter)	8 mm
-----------------------------	------

Electrical properties

Rated current	100 A (Take into account the derating of the contact insert used. The rated current corresponds to the maximum possible
---------------	---

CK8,0-ED-35,00M AG - Crimp contact



1550053

<https://www.phoenixcontact.com/us/products/1550053>

	connection cross-section.)
--	----------------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK8,0-ED-35,00M AG - Crimp contact



1550053

<https://www.phoenixcontact.com/us/products/1550053>

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 10.0	EC000796
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK8,0-ED-35,00M AG - Crimp contact



1550053

<https://www.phoenixcontact.com/us/products/1550053>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com