

SAC-5P-M12MS/40-921/FS 2ST AV - Bus system cable



1579129

<https://www.phoenixcontact.com/us/products/1579129>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, CANopen®, DeviceNet™, 5-position, PUR halogen-free, black RAL 9005, shielded, Plug straight M12, coding: A, on Socket straight M12 SPEEDCON, coding: A, cable length: 40 m, Customer versions

Commercial data

Item number	1579129
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF04
Product key	AF1CDD
GTIN	4046356518512
Weight per piece (including packing)	2,416 g
Weight per piece (excluding packing)	2,400 g
Customs tariff number	85444290
Country of origin	PL

SAC-5P-M12MS/40-921/FS 2ST AV - Bus system cable



1579129

<https://www.phoenixcontact.com/us/products/1579129>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	5

Interfaces

Bus system	CANopen®/DeviceNet™
Signal type/category	CANopen® DeviceNet™

Electrical properties

Nominal voltage U_N	48 V AC 60 V DC
-----------------------	--------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Connector

Connection 1

Type	Plug straight M12
Number of positions	5
Coding type	A (Standard)


Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	5
Locking type	SPEEDCON
Coding type	A (Standard)

Cable/line

Cable length	40 m
--------------	------

CANopen®/DeviceNet™, PUR, black [921]

Dimensional drawing	
UL AWM Style	21198 (80°C/300 V)

SAC-5P-M12MS/40-921/FS 2ST AV - Bus system cable



1579129

<https://www.phoenixcontact.com/us/products/1579129>

Number of positions	4
Shielded	yes
Cable type	CANopen®/DeviceNet™, PUR, black [921]
Conductor structure	2xAWG24/19+2xAWG22/19
AWG signal line	24
AWG power supply	22
Conductor cross-section	2x 0.25 mm ² (Data cable) 2x 0.34 mm ² (Power supply) 1x 0.34 mm ² (Drain wire)
Wire diameter incl. insulation	1.95 mm ±0.05 mm (Data cable) 1.4 mm ±0.05 mm (Power supply)
External cable diameter	6.70 mm ±0.3 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material wire insulation	Foamed PE (Data cable) PE (Power supply)
Single wire, color	red-black, blue-white
Twisted pairs	2 cores to the pair
Overall twist	2 pairs around a drain wire in the center to the core
Optical shield covering	80 %
Insulation resistance	≥ 5 GΩ*km (Data cable) ≥ 5 GΩ*km (Power supply)
Wave impedance	120 Ω ±10 % (with 1 MHz)
Nominal voltage, cable	≤ 300 V (Peak value, not for high-power applications)
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 70 mm, Bending radius: 15 x D, Traversing path: 4.5 m, Traversing rate: 3 m/s, Acceleration: 3 m/s ² , Ambient temperature: -20 °C ... 60 °C
Shield attenuation	≤ 22.9 dB/km (with 1 MHz) ≤ 16.4 dB/km (At 500 kHz) ≤ 9.5 dB/km (At 125 kHz)
Halogen-free	in accordance with DIN VDE 0472 part 815 according to IEC 60754-1
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1) UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2) IEC 60332-1-2 in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -30 °C ... 70 °C (Cable, flexible installation) -20 °C ... 60 °C (for installation)

SAC-5P-M12MS/40-921/FS 2ST AV - Bus system cable



1579129

<https://www.phoenixcontact.com/us/products/1579129>

-20 °C ... 60 °C (cable, drag chain applications)

SAC-5P-M12MS/40-921/FS 2ST AV - Bus system cable



1579129

<https://www.phoenixcontact.com/us/products/1579129>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-M12MS/40-921/FS 2ST AV - Bus system cable



1579129

<https://www.phoenixcontact.com/us/products/1579129>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	26.566 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com