

# Q 1,5/4IDC/24-24KU-KU-ASI-BK - Conductor connector



1585058

<https://www.phoenixcontact.com/us/products/1585058>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Flat conductor connector with QUICKON fast connection technology, 4-pos., for connecting one or two AS-interface flat conductors

## Your advantages

- Robust throughout: housing with IP65/IP67 protection for a wide range of applications

## Commercial data

Item number	1585058
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF50
Product key	AF6HCC
GTIN	4046356168298
Weight per piece (including packing)	40.4 g
Weight per piece (excluding packing)	38.2 g
Customs tariff number	85366990
Country of origin	PL

# Q 1,5/4IDC/24-24KU-KU-ASI-BK - Conductor connector

1585058

<https://www.phoenixcontact.com/us/products/1585058>

## Technical data

### Mounting

Assembly note	If the conductor is reconnected, it must be cut off above the last contact point. QUICKON components may only be operated when under no load.
---------------	---

### Product properties

Product type	Cable connector
Number of positions	4
Position marking	1, 2
Number of connections	4
Number of connections per position	1
Coding	no

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Dimensions

Dimensional drawing	
Width	24 mm
Height	24 mm
Length	86 mm
Diameter	24 mm

### Connection data

#### Connection technology

Frequency of connections between conductors of the same cross section	max. 10 (For the same conductor cross-section)
---	--

#### Conductor connection

Tightening torque	3 Nm
Tightening torque Union nut	3 Nm
Wrench size Union nut	19 mm
Wrench size Contact carrier	24 mm

### Electrical properties

Rated surge voltage (II/2)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (III/3)	6 kV

# Q 1,5/4IDC/24-24KU-KU-ASI-BK - Conductor connector



1585058

<https://www.phoenixcontact.com/us/products/1585058>

Rated current	15 A
Rated voltage (III/3)	30 V
Nominal voltage $U_N$	500 V AC
	500 V DC
Nominal current $I_N$	15 A

## Material specifications

Color	black (RAL 9005)
Material Housing	PA
Material Contact	Copper alloy
Material Contact surface	Sn
Flammability rating according to UL 94	V0
Material wire insulation	PVC / PE

## Cable/line

Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 class 1 to 6/min. 0.15 mm
Wire diameter including insulation	1.8 mm ... 3 mm
Position marking	1, 2
Material wire insulation	PVC/PE/TPE/rubber

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
Impact strength	IK06
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 80 °C
Temperature when conductor connected	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

# Q 1,5/4IDC/24-24KU-KU-ASI-BK - Conductor connector



1585058

<https://www.phoenixcontact.com/us/products/1585058>

## Drawings

Dimensional drawing



# Q 1,5/4IDC/24-24KU-KU-ASI-BK - Conductor connector




1585058

<https://www.phoenixcontact.com/us/products/1585058>

## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1585058>

 <b>cUL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	250 V	11 A	-	-

 <b>UL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	250 V	15 A	-	-

 <b>EAC</b> Approval ID: RU C-DE.AI30.B.01102				
---	--	--	--	--

 <b>EAC</b> Approval ID: RU C-DE.A*30.B.01102				
---	--	--	--	--

 <b>VDE approval of drawings</b> Approval ID: 40032336				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	500 V	-	-	0.75 - 1.5

# Q 1,5/4IDC/24-24KU-KU-ASI-BK - Conductor connector



1585058

<https://www.phoenixcontact.com/us/products/1585058>

## Classifications

### ECLASS

ECLASS-13.0	27440605
ECLASS-15.0	27440605

### ETIM

ETIM 10.0	EC002560
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# Q 1,5/4IDC/24-24KU-KU-ASI-BK - Conductor connector



1585058

<https://www.phoenixcontact.com/us/products/1585058>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	1.356 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)