

HC-26P1N124300 - Device connector rear mounting



1590280

<https://www.phoenixcontact.com/us/products/1590280>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 28-pos.
product version

Device connector rear mounting, application: Signal, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Pin, Radial O-ring, shielded: yes, number of positions: 26, connection method: Solder connection, series: HC

Commercial data

Item number	1590280
Packing unit	24 pc
Minimum order quantity	24 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAJR
GTIN	4046356186544
Weight per piece (including packing)	47.07 g
Weight per piece (excluding packing)	47.07 g
Customs tariff number	85366990
Country of origin	DE

HC-26P1N124300 - Device connector rear mounting



1590280

<https://www.phoenixcontact.com/us/products/1590280>

Technical data

Mounting

Mounting type	Rear mounting/square flange (4x M3)
---------------	-------------------------------------

Product properties

Product type	Circular connectors (device side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Thread type	M27

Material specifications

Flammability rating according to UL 94	V0
Seal material	FPM or NBR or EPDM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA66
Contact material	CuZn
Contact surface	Nickel-plated, gold coating
Gasket and O-ring material	NBR

Electrical properties

Contact

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	8 A
Nominal voltage U _N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

Connection method	Solder connection
Contact connection type	Pin

HC-26P1N124300 - Device connector rear mounting



1590280

<https://www.phoenixcontact.com/us/products/1590280>

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

Connector

Type	straight
Direction of rotation	Standard

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

1590280

<https://www.phoenixcontact.com/us/products/1590280>


Drawings

Dimensional drawing



Installation dimensions

Schematic diagram



Connector pin assignment

HC-26P1N124300 - Device connector rear mounting



1590280

<https://www.phoenixcontact.com/us/products/1590280>

Classifications

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1590280

<https://www.phoenixcontact.com/us/products/1590280>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	04d10b7f-bcc0-42e2-9f2b-4879f5d9f8b5

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com