

NC-0000000MSFZ - Coupler connector



1592034

<https://www.phoenixcontact.com/us/products/1592034>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, application: Signal, straight with plastic cover, Screw locking mechanism, M23, number of positions: 12, contact connection type: Socket, shielded: yes, cable diameter range: 2 mm ... 10.5 mm, connection method: Crimp connection, series: NC, This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1592034
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB35
Product key	ABRIEA
GTIN	4046356190282
Weight per piece (including packing)	36.055 g
Weight per piece (excluding packing)	32.587 g
Customs tariff number	85366990
Country of origin	DE

NC-0000000MSFZ - Coupler connector



1592034

<https://www.phoenixcontact.com/us/products/1592034>

Technical data

Product properties

Product type	Circular connector (cable-side)
Series	NC
Application	Signal
Connection profile	12
Shielded	yes
Thread type	M23

Connection data

Conductor connection

Connection method	Crimp connection
	Crimp connection
	Crimp connection

Connector

Type	straight with plastic cover
------	-----------------------------

Cable/line

External cable diameter	2 mm ... 10.5 mm
-------------------------	------------------

NC-0000000MSFZ - Coupler connector



1592034

<https://www.phoenixcontact.com/us/products/1592034>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

NC-0000000MSFZ - Coupler connector



1592034

<https://www.phoenixcontact.com/us/products/1592034>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com