

# RC-06P1N122200 - Device connector front mounting



1593103

<https://www.phoenixcontact.com/us/products/1593103>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Solder cup, Flat gasket, flange dimensions: 25 mm x 25 mm, Panel thickness min.: 1 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1339315

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1593103       |
| Packing unit                         | 40 pc         |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB31          |
| Product key                          | ABRAFL        |
| GTIN                                 | 4046356194297 |
| Weight per piece (including packing) | 33.7 g        |
| Weight per piece (excluding packing) | 31.86 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# RC-06P1N122200 - Device connector front mounting



1593103

<https://www.phoenixcontact.com/us/products/1593103>

## Technical data

### Product properties

|              |                                   |
|--------------|-----------------------------------|
| Product type | Circular connectors (device side) |
|--------------|-----------------------------------|

### Connector

#### Insulating body

|   |  |
|---|--|
| Coding  | N  |
| Material (Insulating body)                      | PBT                                      |
| Material (Contact)                              | CuZn                                     |
| Material (Contact surface)                      | Ni/Au                                    |
| Insertion/withdrawal cycles                     | 50                                       |
| Connection method                               | Solder cup                               |
| Contact switching type                          | Pin                                      |
| Application                                     | Signal                                   |
| Number of positions                             | 6  |
| Direction of rotation                           | Standard                                 |
| Connection profile                              | 6  |
| Number (Contact group 1)                        | 6  |
| Litz wires Min. cross section (Contact group 1) | 0.08 mm <sup>2</sup>                     |
| Litz wires Max. cross section (Contact group 1) | 2.5 mm <sup>2</sup>                      |
| Rated current Contact (Contact group 1)         | 20 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1)         | 48 V AC<br>74 V DC                       |
| Rated surge voltage                             | 1.5 kV                                   |
| Overvoltage category                            | III                                      |
| Degree of pollution                             | 3  |

#### Housing

|                                   |  |
|-----------------------------------|--|
| Type                              | Flange housing                             |
| Thread type                       | M23  |
| Design                            | straight                                   |
| Type of locking                   | Screw locking mechanism                    |
| Pg screw connection               | none                                       |
| Mounting type                     | Front mounting/square flange (4x Ø 2.7 mm) |
| Flange dimensions                 | 25 mm x 25 mm                              |
| Material (Housing)                | GD-Zn                                      |
| Material (Housing surface)        | Ni   |
| Material (Rotating parts)         | CuZn                                       |
| Degree of protection (plugged in) | IP67                                       |
| Seal for the device               | Flat gasket                                |

# RC-06P1N122200 - Device connector front mounting

1593103

<https://www.phoenixcontact.com/us/products/1593103>

## Drawings



## Installation dimensions


# RC-06P1N122200 - Device connector front mounting

1593103

<https://www.phoenixcontact.com/us/products/1593103>



Schematic diagram



Connector pin assignment

# RC-06P1N122200 - Device connector front mounting



1593103

<https://www.phoenixcontact.com/us/products/1593103>

Schematic diagram



Dimensional drawing

1593103

<https://www.phoenixcontact.com/us/products/1593103>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440109 |
| ECLASS-15.0 | 27440109 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003569 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

1593103

<https://www.phoenixcontact.com/us/products/1593103>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | f9f046a3-44e8-45c7-9e3b-ef66d6617a72 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)