

# RC-06S1N121000 - Cable connector



1593647

<https://www.phoenixcontact.com/us/products/1593647>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Socket, Solder cup, coding: N

## Commercial data

Item number	1593647
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356197250
Weight per piece (including packing)	75.36 g
Weight per piece (excluding packing)	75.36 g
Country of origin	DE

# RC-06S1N121000 - Cable connector



1593647

<https://www.phoenixcontact.com/us/products/1593647>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
Type of the screw connection	-
Pg screw connection	none

### Mechanical properties

#### Mechanical data

Type of the screw connection	-
------------------------------	---

### Connector

#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Number (Contact group 1)	6
Contact diameter (Contact group 1)	2 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm <sup>2</sup>
Litz wires Max. cross section (Contact group 1)	2.5 mm <sup>2</sup>
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	Metal
Degree of protection (plugged in)	IP65

# RC-06S1N121000 - Cable connector



1593647

<https://www.phoenixcontact.com/us/products/1593647>

---

IP67

# RC-06S1N121000 - Cable connector

1593647

<https://www.phoenixcontact.com/us/products/1593647>

## Drawings

Schematic diagram



Connector pin assignment

# RC-06S1N121000 - Cable connector



1593647

<https://www.phoenixcontact.com/us/products/1593647>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)