

# RC-09P1N12T049 - Cable connector



1595283

<https://www.phoenixcontact.com/us/products/1595283>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M23, Cable connector, application: Signal, series: RC, angled, shielded: yes, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Pin, Solder cup, cable diameter range: 6.5 mm ... 7.5 mm, coding: N



The figure shows the 12-pos.  
product version

## Commercial data

Item number	1595283
Packing unit	8 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFC
GTIN	4046356377959
Weight per piece (including packing)	169.46 g
Weight per piece (excluding packing)	141.568 g
Customs tariff number	85366990
Country of origin	DE

# RC-09P1N12T049 - Cable connector



1595283

<https://www.phoenixcontact.com/us/products/1595283>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number (Contact group 1)	1
Contact diameter (Contact group 1)	2 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm <sup>2</sup>
Litz wires Max. cross section (Contact group 1)	2.5 mm <sup>2</sup>
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	8
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm <sup>2</sup>
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

#### Housing

Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn

# RC-09P1N12T049 - Cable connector



1595283

<https://www.phoenixcontact.com/us/products/1595283>

Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)
Degree of protection (plugged in)	IP67

## Seal

External cable diameter	6.5 mm ... 7.5 mm
-------------------------	-------------------

# RC-09P1N12T049 - Cable connector



1595283

<https://www.phoenixcontact.com/us/products/1595283>

## Drawings

Schematic diagram



Connector pin assignment

# RC-09P1N12T049 - Cable connector

1595283

<https://www.phoenixcontact.com/us/products/1595283>

Schematic diagram




Connector pin assignment

# RC-09P1N12T049 - Cable connector

1595283

<https://www.phoenixcontact.com/us/products/1595283>

Schematic diagram




Connector pin assignment

# RC-09P1N12T049 - Cable connector

1595283

<https://www.phoenixcontact.com/us/products/1595283>

Schematic diagram



Dimensional drawing

# RC-09P1N12T049 - Cable connector



1595283

<https://www.phoenixcontact.com/us/products/1595283>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-09P1N12T049 - Cable connector



1595283

<https://www.phoenixcontact.com/us/products/1595283>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	eaae8230-6edd-43f7-bd2f-8b25449c3fb3

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)