

# RC-12P1N12C364 - Rear panel feed-through



1597167

<https://www.phoenixcontact.com/us/products/1597167>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Rear panel feed-through, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Pin, Solder cup, Radial O-ring, Panel thickness max.: 2.5 mm, cable diameter range: 6.5 mm ... 7.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1597167       |
| Packing unit                         | 20 pc         |
| Minimum order quantity               | 1 pc          |
| Product key                          | ABRAFJ        |
| GTIN                                 | 4046356214704 |
| Weight per piece (including packing) | 86.653 g      |
| Weight per piece (excluding packing) | 86.653 g      |
| Country of origin                    | DE            |

# RC-12P1N12C364 - Rear panel feed-through



1597167

<https://www.phoenixcontact.com/us/products/1597167>

## Technical data

### Product properties

|              |                                   |
|--------------|-----------------------------------|
| Product type | Circular connectors (device side) |
|--------------|-----------------------------------|

### Connector

#### Insulating body

|   |   |
|---|---|
| Coding  | N                                       |
| Material (Insulating body)                      | PBT                                     |
| Material (Contact)                              | CuZn                                    |
| Material (Contact surface)                      | Ni/Au                                   |
| Insertion/withdrawal cycles                     | 100                                     |
| Connection method                               | Solder cup                              |
| Contact switching type                          | Pin                                     |
| Application                                     | Signal                                  |
| Number of positions                             | 12                                      |
| Direction of rotation                           | Standard                                |
| Connection profile                              | 12                                      |
| Number (Contact group 1)                        | 12                                      |
| Contact diameter (Contact group 1)              | 1 mm                                    |
| Litz wires Min. cross section (Contact group 1) | 0.08 mm <sup>2</sup>                    |
| Litz wires Max. cross section (Contact group 1) | 1 mm <sup>2</sup>                       |
| Rated current Contact (Contact group 1)         | 8 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1)         | 48 V AC<br>74 V DC                      |
| Rated surge voltage                             | 1.5 kV                                  |
| Overvoltage category                            | III                                     |
| Degree of pollution                             | 3                                       |

#### Housing

|                                   |  |
|-----------------------------------|--|
| Order information:                | Order contact inserts and cable clamping/shield accessories separately |
| Type                              | Feed-through header  |
| Thread type                       | M23  |
| Design                            | straight   |
| Type of locking                   | Screw locking mechanism  |
| Pg screw connection               | none   |
| Mounting type                     | Rear mounting/square flange (4x M3)                                    |
| Housing material                  | Metal  |
| Degree of protection (plugged in) | IP67   |
| Seal for the device               | Radial O-ring  |

#### Seal

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 6.5 mm ... 7.5 mm |
|-------------------------|-------------------|

# RC-12P1N12C364 - Rear panel feed-through




1597167

<https://www.phoenixcontact.com/us/products/1597167>

## Drawings

Schematic diagram



Connector pin assignment

# RC-12P1N12C364 - Rear panel feed-through



1597167

<https://www.phoenixcontact.com/us/products/1597167>

Schematic diagram



Dimensional drawing

# RC-12P1N12C364 - Rear panel feed-through



1597167

<https://www.phoenixcontact.com/us/products/1597167>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440109 |
| ECLASS-15.0 | 27440109 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003569 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

1597167

<https://www.phoenixcontact.com/us/products/1597167>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                     |
|-------------------------------------|-------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                |
| SCIP                                | a555aa80-96f6-4567-a3a3-cb3437bbffd |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)