

RC-12S1N121600 - Cable connector



1598494

<https://www.phoenixcontact.com/us/products/1598494>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Solder cup, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1340703

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1598494 |
| Packing unit | 20 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB31 |
| Product key | ABRAFA |
| GTIN | 4046356220873 |
| Weight per piece (including packing) | 82.882 g |
| Weight per piece (excluding packing) | 78.74 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

RC-12S1N121600 - Cable connector



1598494

<https://www.phoenixcontact.com/us/products/1598494>

Technical data

Notes

| | |
|--------------------|-------------------------------|
| Order information: | Order cable glands separately |
|--------------------|-------------------------------|

Product properties

| | |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Thread type | M23 |

Material specifications

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Connector

Insulating body

| | |
|---|---|
| Coding | N |
| Material (Insulating body) | PBT |
| Material (Contact) | CuZn |
| Material (Contact surface) | Ni/Au |
| Insertion/withdrawal cycles | 50 |
| Connection method | Solder cup |
| Contact switching type | Socket |
| Application | Signal |
| Number of positions | 12 |
| Direction of rotation | Standard |
| Connection profile | 12 |
| Number (Contact group 1) | 12 |
| Contact diameter (Contact group 1) | 1 mm |
| Litz wires Min. cross section (Contact group 1) | 0.08 mm ² |
| Litz wires Max. cross section (Contact group 1) | 1 mm ² |
| Rated current Contact (Contact group 1) | 8 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1) | 48 V AC 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |

Housing

| | |
|---------------------|-------------------------|
| Type | Cable connector housing |
| Thread type | M23 |
| Design | straight |
| Type of locking | Screw locking mechanism |
| Pg screw connection | Pg11 |
| Mounting type | Screw mounting (Pg11) |

RC-12S1N121600 - Cable connector



1598494

<https://www.phoenixcontact.com/us/products/1598494>

| | |
|-----------------------------------|-------|
| Material (Housing) | Metal |
| Degree of protection (plugged in) | IP65 |
| | IP67 |

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP67 |
|----------------------|------|

RC-12S1N121600 - Cable connector

1598494

<https://www.phoenixcontact.com/us/products/1598494>

Drawings

Schematic diagram



Connector pin assignment

RC-12S1N121600 - Cable connector



1598494

<https://www.phoenixcontact.com/us/products/1598494>

Schematic diagram



Dimensional drawing

RC-12S1N121600 - Cable connector



1598494

<https://www.phoenixcontact.com/us/products/1598494>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

RC-12S1N121600 - Cable connector



1598494

<https://www.phoenixcontact.com/us/products/1598494>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 7400dfb5-a691-4e77-b1da-3f4d1de747c4 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com