

# RC-12S1N8A1L00 - Cable connector



1599155

<https://www.phoenixcontact.com/us/products/1599155>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos. product version, with standard DIN cable gland

M23, Cable connector, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1629213

## Commercial data

Item number	1599155
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFA
GTIN	4046356224307
Weight per piece (including packing)	98.88 g
Weight per piece (excluding packing)	92.91 g
Customs tariff number	85366990
Country of origin	DE

# RC-12S1N8A1L00 - Cable connector



1599155

<https://www.phoenixcontact.com/us/products/1599155>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

### Product properties

Product type	Circular connector (cable-side)
Type of the screw connection	IP68 screw
Thread type	M23

### Material specifications

Flammability rating according to UL 94	V0
--	----

### Mechanical properties

#### Mechanical data

Type of the screw connection	IP68 screw
------------------------------	------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none

# RC-12S1N8A1L00 - Cable connector



1599155

<https://www.phoenixcontact.com/us/products/1599155>

Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65
	IP67

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Permissible humidity (storage/transport)	50 % ... 65 %

# RC-12S1N8A1L00 - Cable connector



1599155

<https://www.phoenixcontact.com/us/products/1599155>

## Drawings

Schematic diagram



Connector pin assignment

# RC-12S1N8A1L00 - Cable connector



1599155

<https://www.phoenixcontact.com/us/products/1599155>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-12S1N8A1L00 - Cable connector



1599155

<https://www.phoenixcontact.com/us/products/1599155>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d3a7aec8-6280-4147-892e-54e8c78021f9

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)