

XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Starter kit, consisting of test-disconnect terminal blocks with Push-X connection technology, marking material, bridging and test accessories. A terminal strip for a three-phase transformer circuit (current and voltage) can be configured individually.



Push-X Technology 
Designed by Phoenix Contact

Commercial data

Item number	1565264
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE25
Product key	BE2533
GTIN	4067923044265
Weight per piece (including packing)	451.45 g
Weight per piece (excluding packing)	451.45 g
Customs tariff number	85369010
Country of origin	PL

XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

Set consists of

XTVMEA 6 - Test disconnect terminal block

1446173

<https://www.phoenixcontact.com/us/products/1446173>




Test disconnect terminal block, nom. voltage: 800 V, nominal current: 30 A, connection method: Push-X-connection, Rated cross section: 6 mm², cross section: 0.5 mm² - 10 mm², color: gray

XTVMED 6-PE - Protective conductor terminal block

1446171

<https://www.phoenixcontact.com/us/products/1446171>



Protective conductor terminal block, connection method: Push-X-connection, Rated cross section: 6 mm², cross section: 0.5 mm² - 10 mm², color: green-yellow

XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

D-XTVMEA 6 - End cover

1447809

<https://www.phoenixcontact.com/us/products/1447809>

End cover, depth: 41.9 mm, width: 2.2 mm, height: 104.4 mm, color: gray



SB-MEA 2-8 - Bridge bar

1290589

<https://www.phoenixcontact.com/us/products/1290589>

Bridge bar, number of positions: 2, color: red



XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

C-MEA 6/2 - Operating lever

1394612

<https://www.phoenixcontact.com/us/products/1394612>



Operating lever, depth: 24.4 mm, width: 16.3 mm, height: 15.9 mm, number of positions: 2, color: orange

FBS 1/3/5-8 - Plug-in bridge

3032389

<https://www.phoenixcontact.com/us/products/3032389>



Plug-in bridge, pitch: 8.2 mm, number of positions: 5, nominal current: 41 A, pin assignment: 1,3,5, color: red

XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

FBS 2-8 - Plug-in bridge

3030284

<https://www.phoenixcontact.com/us/products/3030284>



Plug-in bridge, pitch: 8.2 mm, number of positions: 2, nominal current: 41 A, color: red

PAI-4-FIX YE - Test adapter

3032745

<https://www.phoenixcontact.com/us/products/3032745>



Test adapter, Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in, for 4 mm test plug and terminal blocks with 8.2 mm pitch, number of positions: 1, color: yellow

XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

PAI-4-FIX GN - Test adapter

3032758

<https://www.phoenixcontact.com/us/products/3032758>



Test adapter, Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in, for 4 mm test plug and terminal blocks with 8.2 mm pitch, number of positions: 1, color: green

PAI-4-FIX VT - Test adapter

3032761

<https://www.phoenixcontact.com/us/products/3032761>



Test adapter, Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in, for 4 mm test plug and terminal blocks with 8.2 mm pitch, number of positions: 1, color: violet

XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

PAI-4-FIX BU - Test adapter

3032729

<https://www.phoenixcontact.com/us/products/3032729>



Test adapter, Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in, for 4 mm test plug and terminal blocks with 8.2 mm pitch, number of positions: 1, color: blue

S-ME 6 - Switching lock

3034439

<https://www.phoenixcontact.com/us/products/3034439>



Switching lock, width: 8.2 mm, height: 12 mm, color: white

XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

CLIPFIX 35-5 - End bracket

3022276

<https://www.phoenixcontact.com/us/products/3022276>



Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, with parking option for FBS...5, FBS...6, KSS 5, KSS 6, width: 5.15 mm, color: gray

KLM 3 - Terminal strip marker carrier

0811969

<https://www.phoenixcontact.com/us/products/0811969>



Terminal strip marker carrier, adjustable height, for CLIPFIX 15, CLIPFIX 35, and CLIPFIX 35-5 end brackets, can be marked using labels in 20 x 8 mm format

XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

UC-TM 8 CUS - Marker for terminal blocks

0824597

<https://www.phoenixcontact.com/us/products/0824597>



Marker for terminal blocks, can be ordered: by sheet, white (RAL 9010), labeled according to customer specifications, mounting type: latching, for terminal block width: 8.2 mm, Number of individual labels: 56, text field height: 10.5 mm, text field width: 7.6 mm

UC-TMF 8 CUS - Marker for terminal blocks

0824654

<https://www.phoenixcontact.com/us/products/0824654>



Marker for terminal blocks, can be ordered: by sheet, white (RAL 9010), labeled according to customer specifications, mounting type: latching, for terminal block width: 8.2 mm, Number of individual labels: 56, text field height: 5.1 mm, text field width: 7.6 mm

XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

Technical data

Product properties

Product type	Starter kit
--------------	-------------

Connection data

Connection method	Push-X-connection
-------------------	-------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15

XTVMEA 6 SET METERING - Starter kit



1565264

<https://www.phoenixcontact.com/us/products/1565264>

Classifications

ECLASS

ECLASS-13.0	27250390
ECLASS-15.0	27250390

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

XTVMEA 6 SET METERING - Starter kit



1565264
<https://www.phoenixcontact.com/us/products/1565264>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com