

RC-19S1NP20000 - Contact insert



1602968

<https://www.phoenixcontact.com/us/products/1602968>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 16+3, contact connection type: Socket, Solder-in connection, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241566

Commercial data

Item number	1602968
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFU
GTIN	4046356242646
Weight per piece (including packing)	12.8 g
Weight per piece (excluding packing)	12.8 g
Customs tariff number	85366990
Country of origin	DE

RC-19S1NP20000 - Contact insert



1602968

<https://www.phoenixcontact.com/us/products/1602968>

Technical data

Product properties

Product type	Contact insert
Application	Signal
Number of positions	19
Connection profile	16+3
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	1.5 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	10 A (for max. connection cross section)
Nominal voltage U _N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Contact: Contact group 2

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²

Connection data

Connection method	Solder-in connection
-------------------	----------------------

Connector

Direction of rotation	Standard
-----------------------	----------

RC-19S1NP20000 - Contact insert



1602968

<https://www.phoenixcontact.com/us/products/1602968>

Classifications

ECLASS

ECLASS-13.0

27440223

UNSPSC

UNSPSC 21.0

39121400

RC-19S1NP20000 - Contact insert



1602968

<https://www.phoenixcontact.com/us/products/1602968>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com