RC-Z2052 - Cable gland

1604216

https://www.phoenixcontact.com/us/products/1604216

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: Brass, nickel-plated, external cable diameter 8 mm ... 12 mm, shielding: no, connecting thread: Pg11, series: RC, this item is expected to be lead-free from Q3 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1604216
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFT
GTIN	4046356248129
Weight per piece (including packing)	33.39 g
Weight per piece (excluding packing)	31.309 g
Customs tariff number	74198090
Country of origin	DE

Technical data

Product properties

Product type	Cable screw gland
Series	RC
Type of the screw connection	Double bracket
Shielded	no

Dimensions

Thread type connection side	Pg11

Material specifications

Color	brass color
Material for screw connection	Brass, nickel-plated

Cable/line

External cable diameter	8 mm ... 12 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65

Classifications

ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

ETIM

ETIM 10.0	EC000441

UNSPSC

UNSPSC 21.0	39121300

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com