

HC-B 16-EBUQ-2,5 - Contact insert



1605572

<https://www.phoenixcontact.com/us/products/1605572>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 16+PE, size: B16, number of connections per position: 1, Socket, QUICKON connection, 500 V, 16 A, 0.34 mm² ... 2.5 mm²

Product description

Contact insert

With QUICKON connection technology, the wires are connected with just a turn of the screwdriver. The wires do not have to be stripped first. This reduces connection time by at least 60%.

Your advantages

- Shock and vibration-resistant in accordance with DIN EN 61373

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1605572 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF61 |
| Product key | AF7ABC |
| GTIN | 4017918940669 |
| Weight per piece (including packing) | 96.44 g |
| Weight per piece (excluding packing) | 96.44 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

HC-B 16-EBUQ-2,5 - Contact insert

1605572

<https://www.phoenixcontact.com/us/products/1605572>

Technical data

Mounting

| | |
|---------------|---|
| Assembly note | To ensure correct use, installation in housing with IP54 protection or better is required |
|---------------|---|


Product properties

| | |
|------------------------------------|--|
| Product type | Contact insert with a fixed no. of positions |
| Series | HC-B |
| Type | B16 B32 |
| Number of positions | 16 |
| Connection profile | 16+PE |
| Contact numbering | 1 - 16 |
| Number of connections per position | 1 |
| Contact material type | rolled |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Dimensions

| | |
|---------------------------------|--|
| Dimensional drawing |  |
| Width | 34 mm |
| Height | 37 mm |
| Length | 84.5 mm |
| Drill hole distance, horizontal | 77.5 mm |
| Drill hole distance, vertical | 27 mm |

Mechanical characteristics

| | |
|------------------|--------|
| Contact diameter | 2.5 mm |
|------------------|--------|

Connection data

Connection technology

| | |
|------------------------------------|--------------------|
| Connection technology | QUICKON connection |
| Number of connections per position | 1 |

Conductor connection

| | |
|------------------------------|---|
| Conductor cross-section | 0.34 mm ² ... 2.5 mm ² (Litz wire structure VDE 0295, Class 1 - 5/litz wire diameter \geq 0.2 mm) |
| Connection cross section AWG | 22 ... 14 |

HC-B 16-EBUQ-2,5 - Contact insert



1605572

<https://www.phoenixcontact.com/us/products/1605572>

| | |
|-------------------|--|
| Tightening torque | 0.8 Nm ... 1.2 Nm (PE connection) |
| | 0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing) |

Electrical properties

| | |
|-----------------------|-------|
| Rated voltage (III/3) | 500 V |
| | 500 V |
| Rated surge voltage | 6 kV |
| | 6 kV |
| Rated current | 16 A |
| | 16 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

Material specifications

| | |
|--|--------------|
| Material Wire insulation | PVC / PE |
| Flammability rating according to UL 94 | V0 |
| Contact material | Copper alloy |
| Contact surface material | Ag |
| Contact carrier material | PA |
| Standards/regulations | PA |
| | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|--|
| Ambient temperature (operation) | -40 °C ... 125 °C (including heating up of contacts) |
| Ambient temperature (assembly) | -25 °C ... 50 °C |

Standards and regulations

Testing

| | |
|-----------------------|---|
| Standards/regulations | PA: Fire protection in rail vehicles - requirement sets R22 and R23 acc. to DIN EN 45545-2 (Risk level HL1 - HL2) |
| | PA: Fire protection in rail vehicles - requirement set R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |


HC-B 16-EBUQ-2,5 - Contact insert

1605572

<https://www.phoenixcontact.com/us/products/1605572>


Drawings

Dimensional drawing



Female insert

Dimensional drawing



Mounting cutout when used without housing

HC-B 16-EBUQ-2,5 - Contact insert

1605572

<https://www.phoenixcontact.com/us/products/1605572>




Schematic diagram




Connector pin assignment, connection side

1605572

<https://www.phoenixcontact.com/us/products/1605572>



Derating diagram for flexible conductors



Derating diagram for solid conductors

HC-B 16-EBUQ-2,5 - Contact insert



1605572

<https://www.phoenixcontact.com/us/products/1605572>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1605572>

DNV

Approval ID: TAE000037S



CSA

Approval ID: 013631_6233_01



cUL Recognized

Approval ID: E118976



UL Recognized

Approval ID: E118976

HC-B 16-EBUQ-2,5 - Contact insert



1605572

<https://www.phoenixcontact.com/us/products/1605572>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440205 |
| ECLASS-15.0 | 27440205 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000438 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121500 |
|-------------|----------|

HC-B 16-EBUQ-2,5 - Contact insert



1605572

<https://www.phoenixcontact.com/us/products/1605572>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 1.09 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com