

TU-09P1N12WB00 - Device connector front mounting



1605929

<https://www.phoenixcontact.com/us/products/1605929>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, application: Signal, series: TU, straight, shielded: yes, Bayonet locking, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Pin, Solder cup, Axial O-ring, Panel thickness min.: 1.5 mm, coding: N

Commercial data

Item number	1605929
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAHL
GTIN	4046356255868
Weight per piece (including packing)	41.55 g
Weight per piece (excluding packing)	41.55 g
Country of origin	DE

TU-09P1N12WB00 - Device connector front mounting



1605929

<https://www.phoenixcontact.com/us/products/1605929>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number (Contact group 1)	1
Contact diameter (Contact group 1)	2 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	8
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

Housing

Order information:	Order contact inserts separately
Type	Flange housing
Thread type	M23
Design	straight
Type of locking	Bayonet locking
Pg screw connection	none
Mounting type	Front mounting/square flange (4x Ø 3.2 mm)

TU-09P1N12WB00 - Device connector front mounting



1605929

<https://www.phoenixcontact.com/us/products/1605929>

Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)
Degree of protection (plugged in)	IP67
Seal for the device	Axial O-ring

TU-09P1N12WB00 - Device connector front mounting

1605929


<https://www.phoenixcontact.com/us/products/1605929>



Drawings

Dimensional drawing


4xØ3,2/M3/□19,8±0,1



Installation dimensions

Dimensional drawing

4xØ3,2/M3/□19,8±0,1




Installation dimensions

Schematic diagram



Connector pin assignment

Schematic diagram




Connector pin assignment

1605929

<https://www.phoenixcontact.com/us/products/1605929>

Schematic diagram



Dimensional drawing

TU-09P1N12WB00 - Device connector front mounting



1605929

<https://www.phoenixcontact.com/us/products/1605929>

Classifications

UNSPSC

UNSPSC 21.0	39121413
-------------	----------

1605929

<https://www.phoenixcontact.com/us/products/1605929>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com