


# NBC-P12MSX/ 1,0-94F - Network cable

1584465

<https://www.phoenixcontact.com/us/products/1584465>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT6<sub>A</sub> (10 Gbps), 8-position, PUR halogen-free, water blue RAL 5021, shielded (Advanced Shielding Technology), Plug straight M12, coding: X / IP67, on free cable end, cable length: 1 m

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1584465       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF04          |
| Product key                          | AF1CMJ        |
| GTIN                                 | 4067923121423 |
| Weight per piece (including packing) | 81 g          |
| Weight per piece (excluding packing) | 81 g          |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

1584465

<https://www.phoenixcontact.com/us/products/1584465>

## Technical data

### Product properties

|                     |                         |
|---------------------|-------------------------|
| Product type        | Data cable preassembled |
| Application         | Standard                |
| Number of positions | 8                       |
| Shielded            | yes                     |

### Interfaces

|                      |                                      |
|----------------------|--------------------------------------|
| Bus system           | Ethernet                             |
| Signal type/category | Ethernet CAT6 <sub>A</sub> , 10 Gbps |

### Signaling


|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Electrical properties

|                       |         |
|-----------------------|---------|
| Nominal voltage $U_N$ | 48 V AC |
|                       | 60 V DC |
| Nominal current $I_N$ | 0.5 A   |
| Transmission medium   | Copper  |
| Transmission speed    | 10 Gbps |

### Connector

#### Connection 1

|                             |                                                                                                                                                    |
|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|
| Dimensional drawing         | <br>Pin assignment of M12 plug, 8-pos., X-coded, pin side view |
| Type                        | M12 Plug, straight, 8-position, shielded (Advanced Shielding Technology), Push Pull, Keying: X                                                     |
| Number of positions         | 8                                                                                                                                                  |
| Shielded                    | yes                                                                                                                                                |
| Shielding                   | Advanced Shielding Technology                                                                                                                      |
| Signal type/category        | Ethernet CAT6 <sub>A</sub> (IEC 11801), 10 Gbps                                                                                                    |
| Insertion/withdrawal cycles | ≥ 100                                                                                                                                              |
| Insulation resistance       | ≥ 100 MΩ                                                                                                                                           |
| Overvoltage category        | II                                                                                                                                                 |
| Degree of pollution         | 3                                                                                                                                                  |
| Material Contact            | CuZn                                                                                                                                               |

# NBC-P12MSX/ 1,0-94F - Network cable



1584465

<https://www.phoenixcontact.com/us/products/1584465>

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Material Contact surface               | Ni/Au                                       |
| Material Contact carrier               | PA 6.6                                      |
| Material Grip body                     | TPU, hardly inflammable, self-extinguishing |
| Material Seal                          | FKM                                         |
| Flammability rating according to UL 94 | V0                                          |
| Ambient temperature (operation)        | -25 °C ... 85 °C                            |
| Standard designation                   | M12 connector                               |
| Standards/regulations                  | IEC 61076-2-010                             |

## Connection 2

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

## Cable/line

|              |     |
|--------------|-----|
| Cable length | 1 m |
|--------------|-----|

## Ethernet 10 Gbit [94F]

|                                |                                                                                      |
|--------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing            |  |
| UL AWM Style                   | 21238 (80 °C / 600 V)                                                                |
| Number of positions            | 8                                                                                    |
| Shielded                       | yes                                                                                  |
| Cable type                     | Ethernet 10 Gbit [94F]                                                               |
| Conductor structure            | 4x2xAWG26/7; S/FTP                                                                   |
| AWG signal line                | 26                                                                                   |
| Conductor cross-section        | 4x 2x 0.14 mm <sup>2</sup>                                                           |
| Wire diameter incl. insulation | 1 mm ±0.05 mm                                                                        |
| External cable diameter        | 6.40 mm ±0.2 mm                                                                      |
| Outer sheath, material         | PUR                                                                                  |
| External sheath, color         | water blue RAL 5021                                                                  |
| Conductor material             | Bare Cu litz wires                                                                   |
| Material wire insulation       | Foamed PE                                                                            |
| Single wire, color             | white/blue-blue, white/orange-orange, white/green-green, white/brown-brown           |
| Twisted pairs                  | 2 cores to the pair                                                                  |
| Overall twist                  | 4 pairs for core                                                                     |
| Optical shield covering        | 70 %                                                                                 |
| Insulation resistance          | ≥ 500 MΩ*km                                                                          |
| Loop resistance                | ≤ 290.00 Ω/km                                                                        |
| Wave impedance                 | 100 Ω ±5 Ω (at 100 MHz)                                                              |

# NBC-P12MSX/ 1,0-94F - Network cable



1584465

<https://www.phoenixcontact.com/us/products/1584465>

|                                               |                                                 |
|-----------------------------------------------|-------------------------------------------------|
| Nominal voltage, cable                        | ≤ 100 V                                         |
| Test voltage Core/Core                        | 2000 V (50 Hz, 1 min.)                          |
| Test voltage Core/Shield                      | 2000.00 V (50 Hz, 1 min.)                       |
| Minimum bending radius, fixed installation    | 4 x D                                           |
| Minimum bending radius, flexible installation | 8 x D                                           |
| Smallest bending radius, fixed installation   | 26 mm                                           |
| Smallest bending radius, movable installation | 51 mm                                           |
| Halogen-free                                  | according to IEC 60754-1                        |
| Flame resistance                              | according to IEC 60332-1-2                      |
|                                               | in accordance with UN ECE-R 118.03              |
|                                               | according to CSA C 22.2 No. 210-FT1             |
| Resistance to oil                             | in accordance with DIN EN 60811-404             |
| Ambient temperature (operation)               | -40 °C ... 80 °C (cable, fixed installation)    |
|                                               | -20 °C ... 80 °C (Cable, flexible installation) |

## Environmental and real-life conditions

### Ambient conditions

|                      |           |
|----------------------|-----------|
| Degree of protection | IP67/IP20 |
|----------------------|-----------|


## Drawings

Dimensional drawing



M12 push-pull male connector, straight

Schematic diagram



Pin assignment of M12 plug, 8-pos., X-coded, pin side view

1584465

<https://www.phoenixcontact.com/us/products/1584465>

Circuit diagram



Contact assignment of the M12 plug

# NBC-P12MSX/ 1,0-94F - Network cable



1584465

<https://www.phoenixcontact.com/us/products/1584465>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

# NBC-P12MSX/ 1,0-94F - Network cable



1584465

<https://www.phoenixcontact.com/us/products/1584465>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)