

# TU-12P1N8ATUDU - Cable connector



1605955

<https://www.phoenixcontact.com/us/products/1605955>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: TU, angled, shielded: yes, Bayonet locking, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 2 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1605955
Packing unit	8 pc
Minimum order quantity	8 pc
Sales key	AB31
Product key	ABRAHC
GTIN	4046356256124
Weight per piece (including packing)	176.54 g
Weight per piece (excluding packing)	164.367 g
Customs tariff number	85366990
Country of origin	DE

# TU-12P1N8ATUDU - Cable connector



1605955

<https://www.phoenixcontact.com/us/products/1605955>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Bayonet locking
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)
Degree of protection (plugged in)	IP67

#### Seal

External cable diameter	2 mm ... 14.5 mm
Seal material	NBR

### Environmental and real-life conditions

#### Ambient conditions

# TU-12P1N8ATUDU - Cable connector



1605955

<https://www.phoenixcontact.com/us/products/1605955>

Permissible humidity (storage/transport)
--

50 % ... 65 %
---------------

# TU-12P1N8ATUDU - Cable connector

1605955

<https://www.phoenixcontact.com/us/products/1605955>



## Drawings

Schematic diagram




Connector pin assignment

# TU-12P1N8ATUDU - Cable connector



1605955

<https://www.phoenixcontact.com/us/products/1605955>



# TU-12P1N8ATUDU - Cable connector



1605955

<https://www.phoenixcontact.com/us/products/1605955>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# TU-12P1N8ATUDU - Cable connector



1605955

<https://www.phoenixcontact.com/us/products/1605955>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	02fa8ffe-58ff-4389-a2e1-b998c75bfd4

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)