

# HC-26P1N224300 - Device connector rear mounting



1590307

<https://www.phoenixcontact.com/us/products/1590307>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 28-pos.  
product version

Device connector rear mounting, application: Signal, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Pin, Radial O-ring, 4xM3, shielded: yes, number of positions: 26, connection method: Solder-in connection, series: HC

## Commercial data

Item number	1590307
Packing unit	12 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAJR
GTIN	4046356186704
Weight per piece (including packing)	48.625 g
Weight per piece (excluding packing)	48.625 g
Country of origin	DE

# HC-26P1N224300 - Device connector rear mounting



1590307


<https://www.phoenixcontact.com/us/products/1590307>

## Technical data

### Product properties

Product type	Circular connectors (device side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Thread type	M27

### Dimensions

Dimensional drawing	
Length of the solder pin	3.5 mm 3.5 mm

### Material specifications

Seal material	FPM or NBR or EPDM
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA66
Contact material	CuZn
Contact surface	Nickel-plated, gold coating
Gasket and O-ring material	FPM

### Electrical properties

#### Contact

Contact diameter	1 mm
Nominal current $I_N$	8 A
Nominal voltage $U_N$	150 V
Overvoltage category	II
Degree of pollution	3
Rated surge voltage	1.5 kV

### Connection data

#### Conductor connection

Connection method	Solder-in connection
Contact connection type	Pin

# HC-26P1N224300 - Device connector rear mounting



1590307

<https://www.phoenixcontact.com/us/products/1590307>

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

## Connector

Type	straight
Direction of rotation	Standard


## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m


Drawings

Dimensional drawing



Installation dimensions

Schematic diagram



# HC-26P1N224300 - Device connector rear mounting



1590307

<https://www.phoenixcontact.com/us/products/1590307>

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)