

RC-0000000G600 - Rear panel feed-through



1592832

<https://www.phoenixcontact.com/us/products/1592832>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rear panel feed-through, series: RC, straight, Screw locking mechanism, M23, Axial O-ring, shielded: no, panel thickness max.: 6.5 mm. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1592832 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Product key | ABRAFK |
| GTIN | 4046356193009 |
| Weight per piece (including packing) | 113 g |
| Weight per piece (excluding packing) | 105.65 g |
| Country of origin | DE |

RC-0000000G600 - Rear panel feed-through



1592832

<https://www.phoenixcontact.com/us/products/1592832>

Technical data

Product properties

| | |
|--------------|----------------------------|
| Product type | Circular connector housing |
| Series | RC |
| Application | Signal |
| Shielded | no |
| Thread type | M23 |

Dimensions

| | |
|-----------------|----------|
| Panel thickness | < 6.5 mm |
|-----------------|----------|

Material specifications

| | |
|------------------|-------|
| Material Housing | Metal |
|------------------|-------|

Connector

| | |
|------|----------|
| Type | straight |
|------|----------|

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP67 |
|----------------------|------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | Rear mounting |
| Assembly note | Central fastening |

RC-0000000G600 - Rear panel feed-through



1592832

<https://www.phoenixcontact.com/us/products/1592832>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440224 |
| ECLASS-15.0 | 27440224 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003556 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

1592832

<https://www.phoenixcontact.com/us/products/1592832>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 5b3fa602-0b86-45c7-88dd-d4742faa882b |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com