

UC-1RP1NRAT0DU - Cable connector



1606722

<https://www.phoenixcontact.com/us/products/1606722>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Cable connector, application: Signal, series: UC, angled, shielded: yes, Screw locking mechanism, No. of pos.: 16+2+FE, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 2 mm ... 14.5 mm, coding: N

Commercial data

Item number	1606722
Packing unit	8 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAIC
GTIN	4046356261456
Weight per piece (including packing)	165.7 g
Weight per piece (excluding packing)	154.91 g
Country of origin	DE

UC-1RP1NRAT0DU - Cable connector



1606722

<https://www.phoenixcontact.com/us/products/1606722>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Note	Order information: Order crimp contacts 16 x Ø 1 mm, 2 x Ø 1.5 mm, 1 x Ø 1.5 (PE) separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	19
Direction of rotation	Standard
Connection profile	16+2+FE
Number (Contact group 1)	3
Contact diameter (Contact group 1)	1.5 mm
Rated current Contact (Contact group 1)	10 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	16
Contact diameter (Contact group 2)	1 mm
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

Housing

Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)
Degree of protection (plugged in)	IP67

Seal

UC-1RP1NRAT0DU - Cable connector



1606722

<https://www.phoenixcontact.com/us/products/1606722>

External cable diameter	2 mm ... 14.5 mm
Seal material	NBR

UC-1RP1NRAT0DU - Cable connector



1606722

<https://www.phoenixcontact.com/us/products/1606722>

Drawings

Schematic diagram




Connector pin assignment

UC-1RP1NRAT0DU - Cable connector



1606722

<https://www.phoenixcontact.com/us/products/1606722>



UC-1RP1NRAT0DU - Cable connector



1606722

<https://www.phoenixcontact.com/us/products/1606722>

Classifications

UNSPSC

UNSPSC 21.0	39121409
-------------	----------

UC-1RP1NRAT0DU - Cable connector



1606722

<https://www.phoenixcontact.com/us/products/1606722>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com