

# RF-12P1N8A8003 - Cable connector



1607227

<https://www.phoenixcontact.com/us/products/1607227>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, application: Feedback, signal, straight, Screw locking mechanism, M23, number of positions: 12, contact connection type: Pin, shielded: yes, cable diameter range: 9 mm ... 13.2 mm, number of positions: 12, connection method: Crimp connection, series: RF

## Commercial data

Item number	1607227
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	AB33
Product key	ABRAGA
GTIN	4046356267908
Weight per piece (including packing)	96.83 g
Weight per piece (excluding packing)	50.41 g
Customs tariff number	85366990
Country of origin	DE

# RF-12P1N8A8003 - Cable connector



1607227

<https://www.phoenixcontact.com/us/products/1607227>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

### Product properties

Product type	Circular connector (cable-side)
Series	RF
Application	Feedback, signal Signal
Number of positions	12
Connection profile	12
Shielded	yes
Coding	N
Thread type	M23

### Material specifications

Seal material	FPM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 6.6
Gasket and O-ring material	FPM

### Connection data

#### Conductor connection

Connection method	Crimp connection
-------------------	------------------

### Electrical properties

#### Contact

Contact diameter	1 mm
Nominal current $I_N$	8 A
Nominal voltage $U_N$	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Connector

Type	straight
Direction of rotation	Standard

### Cable/line

# RF-12P1N8A8003 - Cable connector



1607227

<https://www.phoenixcontact.com/us/products/1607227>

External cable diameter	9 mm ... 13.2 mm
-------------------------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	2000 m

# RF-12P1N8A8003 - Cable connector

1607227


<https://www.phoenixcontact.com/us/products/1607227>

## Drawings

Dimensional drawing



Schematic diagram



# RF-12P1N8A8003 - Cable connector



1607227

<https://www.phoenixcontact.com/us/products/1607227>

## Classifications

### UNSPSC

UNSPSC 21.0	39121413
-------------	----------

# RF-12P1N8A8003 - Cable connector



1607227

<https://www.phoenixcontact.com/us/products/1607227>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)