

# RC-06S1NS20000 - Contact insert



1594164

<https://www.phoenixcontact.com/us/products/1594164>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 6, contact connection type: Socket, Screw connection, series: NC, RC, RM, TU, UC

## Commercial data

Item number	1594164
Packing unit	1 pc
Sales key	AB31
Product key	ABRAFU
GTIN	4046356200028
Weight per piece (including packing)	13.57 g
Weight per piece (excluding packing)	7.121 g
Customs tariff number	85389099
Country of origin	DE

# RC-06S1NS20000 - Contact insert



1594164

<https://www.phoenixcontact.com/us/products/1594164>

## Technical data

### Product properties

Product type	Contact insert
Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	6
Connection profile	6
Coding	N
Thread type	M23

### Electrical properties

Contact: Contact group 1

Contact diameter	2 mm
Min. cross section	0.08 mm <sup>2</sup>
Max. cross section	1 mm <sup>2</sup>
Nominal current I <sub>N</sub>	20 A (for max. connection cross section)
Nominal voltage U <sub>N</sub>	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Connection data

Connection method	Screw connection
-------------------	------------------

### Material specifications

Material Insulating body	PBT
Material Contact	CuZn
Material Contact surface	Ni/Au

### Connector

Direction of rotation	Standard
-----------------------	----------

### Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

# RC-06S1NS20000 - Contact insert



1594164

<https://www.phoenixcontact.com/us/products/1594164>

## Classifications

### ECLASS

ECLASS-13.0

27440223

### UNSPSC

UNSPSC 21.0

39121400

# RC-06S1NS20000 - Contact insert



1594164

<https://www.phoenixcontact.com/us/products/1594164>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b7b5976c-9d41-4b6e-a082-b91750ee3498

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)